


TABLE A


PART NO	LENGTH
GS-485HD15	2.0m (6.6 ft.)



NOTES:

1. UL20276 28AWG*2P+AEB
OD: 5.0mm, JACKET WHITE COLOR.
2. RJ12 6P6C MODULAR PLUG.
CONTACT: BRASS, GOLD FLASH.
3. 45P PVC, WHITE COLOR.
1394 6PIN PLUG SOLDREING TYPE.
INSULATION PBT BLACK COLOR
CONTACT BRASS, GOLD FLASH
4. MINIMUM BEND RADIUS - 40 mm [1.57 in]
5. OPERATING TEMPERATURE - 0-60°C (32-140°F)

PIN-OUT DIAGRAM



SVC-232RJ12-CBL-2	
Rev: original	Date: 06/2009
Units: mm [inches]	
Scale: none	
ZIPLINK SureServo Cable	