



PART NO	LENGTH
SVC-PCCFG-CBL	1830mm [72]



PIN-OUT DIAGRAM



NOTES:

1. UL20276 28AWG*2P+AEB
OD: 4.0mm, JACKET WHITE COLOR.
2. IEEE 1394 6M MALE CONNECTOR
3. DB-9F FEMALE CONNECTOR
4. MINIMUM BEND RADIUS – 48 mm [1.9 in]
5. OPERATING TEMPERATURE – 0–60°C (32–140°F)

SVC-PCCFG-CBL
Rev: original Date: 05/2010
Units: mm [inches]
Scale: none
SURE SERVO PC CONFIGURATION COMMUNICATION CABLE
AUTOMATIONDIRECT