



NOTES:

1. CABLE – 25 conductor, 28 AWG+AE, UL2464 OD:7.0MM PVC black jacket
2. VOLTAGE –  
AC/DC rated operating voltage 24V  
AC/DC maximum voltage 30V
3. OPERATING TEMPERATURE– 60C
4. P1 CONNECTOR – 25M MALE BLACK PIN
5. P2 CONNECTOR – 25F FEMALE BLACK PIN
6. MINIMUM BEND RADIUS – 56mm [2.20”]

P1		PIN OUT		P2	
1	BLACK	1	14	BROWN/WHITE	14
2	BROWN	2	15	RED/WHITE	15
3	RED	3	16	ORANGE/WHITE	16
4	ORANGE	4	17	GREEN/WHITE	17
5	YELLOW	5	18	BLUE/WHITE	18
6	GREEN	6	19	VIOLET/WHITE	19
7	BLUE	7	20	RED/BLACK	20
8	VIOLET	8	21	ORANGE/BLACK	21
9	GRAY	9	22	YELLOW/BLACK	22
10	WHITE	10	23	GREEN/BLACK	23
11	PINK	11	24	GRAY/BLACK	24
12	LIGHT-GREEN	12	25	PINK/BLACK	25
13	BLACK/WHITE	13	SHELL	DRAIN	SHELL

ZL-DB25-CBL-2	
Rev: A	Date: 07/2009
Units: mm [inches]	
Scale: .0394	
ZIPLINK DB25 COMMUNICATION CABLE	
	