



NOTES:

1. CABLE – 6 conductor, 26 AWG+TALCUM, UL20251, OD: 2.5\*7.0mm, PVC black jacket
2. VOLTAGE –  
AC/DC rated operating voltage 24V  
AC/DC maximum voltage 30V
3. OPERATING TEMPERATURE – 0–60°C (32–140°F)
4. P1 CONNECTOR – RJ12 6P6C MODULAR PLUG
5. MINIMUM BEND RADIUS – 36mm [1.42\"]

PINOUT	DIAGRAM
P1	P2
WHITE	— 1
BLACK	— 2
RED	— 3
GREEN	— 4
YELLOW	— 5
BLUE	— 6

ZL-RJ12-CBL-2P	
Rev: B	Date: 07/2009
Units: mm [inches]	
Scale: .0394	
ZIPLINK RJ12 PIGTAIL COMMUNICATION CABLE	
	