


NOTES:

1. CABLE – 6 conductor, 26 AWG+TALCUM, UL20251, OD: 2.5*7.0mm, PVC black jacket
2. VOLTAGE –
AC/DC rated operating voltage 24V
AC/DC maximum voltage 30V
3. OPERATING TEMPERATURE– 0–60°C (32–140°F)
4. P1 & P2 CONNECTOR – RJ12 6P6C MODULAR PLUG
5. MINIMUM BEND RADIUS – 36mm [1.42”]

PINOUT		DIAGRAM	
P1			P2
1	WHITE	6	
2	BLACK	5	
3	RED	4	
4	GREEN	3	
5	YELLOW	2	
6	BLUE	1	

ZL-RJ12-CBL-2	
Rev: B	Date: 07/2009
Units: mm [inches]	
Scale: .0394	
ZIPLINK RJ12 COMMUNICATION CABLE	
 AUTOMATIONDIRECT .com	