


TABLE A


PART NO	LENGTH
GS-485HD15	2.0m (6.6 ft.)



NOTES:

1. UL20276 28AWG*2P+AEB
OD: 5.0mm, JACKET BLACK COLOR.
2. HDB 15P MALE SOLDERING TYPE.
INSULATION: PBT, BLACK COLOR.
CONTACT: BRASS, GOLD FLASH.
3. RJ12 6P6C MODULAR PLUG. (圓孔)
CONTACT: BRASS, GOLD FLASH(6u”).
4. THUMB SCREW: M2.6*0.45, AD4*30.5,
BLACK COLOR MOLDING.
5. MINIMUM BEND RADIUS - 40 mm [1.57 in]
6. OPERATING TEMPERATURE - 0-60°C (32-140°F)

PIN-OUT DIAGRAM



GS-485HD15-CBL-2

Rev: original

Date: 06/2009

Units: mm [inches]

Scale: none

ZIPLINK GS Drive Cable