



PART NO	LENGTH
SVC-MDCOM-CBL	915mm [36]



PIN-OUT DIAGRAM



- NOTES:
1. UL20276 28AWG*3P+AEB
OD: 5.0mm, JACKET WHITE COLOR.
 2. IEEE 1394 6M MALE CONNECTOR
 3. HEAT SHRINK TUBE
 4. MINIMUM BEND RADIUS – 60 mm [2.4 in]
 5. OPERATING TEMPERATURE – 0–60°C (32–140°F)

SVC-MDCOM-CBL	
Rev: original	Date: 05/2010
Units: mm [inches]	
Scale: none	
SURE SERVO RS422/485 COMMUNICATION CABLE	
AUTOMATIONDIRECT 