



TABLE A

PART NO.	LENGTH
ZL-BX-CBL15-1P	1.0m (3.3ft)
ZL-BX-CBL15-2P	2.0m (6.6ft)



PIN-OUT DIAGRAM

P1	P2
15	BLUE
	PINK
14	LIGHT BLUE
13	LIGHT GREEN
12	GRAY
11	YELLOW
	PURPLE
5	GREEN
4	ORANGE
3	RED
2	BROWN
1	BLACK
10	ORANGE/BLACK
	RED/BLACK
9	WHITE
8	GREEN/BLACK
7	GRAY/BLACK
6	YELLOW/BLACK
	PURPLE/WHITE
NC	GREEN/WHITE
NC	ORANGE/WHITE
NC	RED/WHITE
NC	BROWN/WHITE
NC	BLACK/WHITE

NOTES:

- CABLE: 24 CONDUCTOR, 24 AWG, PVC JACKET INSULATION RATING 80°C (176°F), 300V
- CURRENT: 2A PER CONDUCTOR, 36A MAXIMUM CABLE CURRENT
- VOLTAGE
  - 240V AC/DC RATED OPERATING VOLTAGE
  - 265V AC/DC MAXIMUM VOLTAGE
- OPERATING TEMPERATURE: 0-60°C (32-140°F)
- P1 CONNECTOR: 15 POSITION OVERMOLDED TERMINAL BLOCK FOR BRX PLC
- P2 CONNECTOR: 24 TINNED PIG-TAIL LEADS
- MINIMUM BEND RADIUS: 65.6MM [2.58IN]

NC WIRES MUST BE CUT BACK AND HEAT SHRINKED

ZL-BX-CBL15-nP	
Rev: C	Date: 4/12/2017
Units: mm [inches]	
Scale: 1:1	
ZIPLink Connector Module Cable	