



TABLE A

PART NO	LENGTH
ZL-DO-CBL24-1P	1.0m [3.3 ft]
ZL-DO-CBL24-2P	2.0m [6.6 ft]

- NOTES:
- CABLE – 24 conductor, 24 AWG, PVC jacket insulation rating 80°C (176°F), 300V
  - CURRENT – 2A per conductor, 40A maximum cable current
  - VOLTAGE – 240V AC/DC rated operating voltage
  - OPERATING TEMPERATURE – 0–60°C (32–140°F)
  - P1 CONNECTOR – 24-pin receptacle equivalent to Molex Micro-Fit3.0 part # 43025–2400
  - P2 CONNECTOR – PIG TAIL
  - MINIMUM BEND RADIUS – 65.6mm [2.58"]

PIN-OUT DIAGRAM

P1	P2	P1	P2
1 — BLUE		13 — ORANGE/BLACK	
2 — PINK		14 — RED/BLACK	
3 — LIGHT BLUE		15 — WHITE	
4 — LIGHT GREEN		16 — GREEN/BLACK	
5 — GRAY		17 — GRAY/BLACK	
6 — YELLOW		18 — YELLOW/BLACK	
7 — PURPLE		19 — PURPLE/WHITE	
8 — GREEN		20 — GREEN/WHITE	
9 — ORANGE		21 — ORANGE/WHITE	
10 — RED		22 — RED/WHITE	
11 — BROWN		23 — BROWN/WHITE	
12 — BLACK		24 — BLACK/WHITE	

ZL-DO-CBL24-nP

Rev: A Date: 10/2009

Units: mm [inches]

Scale: .03940

ZIPLINK DL05/DL06 Cable

AUTOMATIONDIRECT