



NOTES:

1. CABLE – 15 conductor, 28 AWG+AE, UL2464, OD:6.0MM, PVC black jacket
2. VOLTAGE –
AC/DC rated operating voltage 24V
AC/DC maximum voltage 30V
3. OPERATING TEMPERATURE– 60C
4. P1 CONNECTOR –DB–15M MALE BLACK PIN/GF SHELL–NICKEL PLATING
5. P2 CONNECTOR –DB–15F FEMALE BLACK PIN/GF SHELL–NICKEL PLATING
6. MINIMUM BEND RADIUS – 48mm [1.89”]

P1	PIN	OUT	P2
1	BLACK		1
2	BROWN		2
3	RED		3
4	ORANGE		4
5	YELLOW		5
6	GREEN		6
7	BLUE		7
8	VIOLET		8
9	GRAY		9
10	WHITE		10
11	PINK		11
12	LIGHT-GREEN		12
13	LIGHT-BLUE		13
14	BLACK/WHITE		14
15	RED/WHITE		15
SHELL	DRAIN		SHELL

ZL-DB15-CBL-2	
Rev: A	Date: 07/2009
Units: mm [inches]	
Scale: .0394	
ZIPLINK DB15 COMMUNICATION CABLE	
	