



NOTES:

1. CABLE – 9 conductor, 28 AWG+AE, UL2464, OD:5.0MM, PVC black jacket
2. VOLTAGE –
AC/DC rated operating voltage 24V
AC/DC maximum voltage 30V
3. OPERATING TEMPERATURE – 0–60°C (32–140°F)
4. P1 CONNECTOR –DB–9M MALE BLACK PIN/GF SHELL–NICKEL PLATING
5. P2 CONNECTOR –DB–9F FEMALE BLACK PIN/GF SHELL–NICKEL PLATING
6. MINIMUM BEND RADIUS – 40mm [1.57”]

PIN-OUT DIAGRAM

P1		P2
1	BLACK	1
2	BROWN	2
3	RED	3
4	ORANGE	4
5	YELLOW	5
6	GREEN	6
7	BLUE	7
8	VIOLET	8
9	GRAY	9
SHELL	DRAIN	SHELL

ZL-DB9-CBL-2	
Rev: original	Date: 06/2009
Units: mm [inches]	
Scale: none	
ZIPLINK DB9 COMMUNICATION CABLE	
	