

Accessories for OPT2024 - OPT2025

Photoelectric Sensors

Right-angle Mounting Brackets

Mounting bracket, right-angle, vertical adjustment, nickel plated steel. For use with OPT2024-OPT2025 photoelectric sensors.

| Mounting Brackets for OPT Series Photoelectric Sensors | | | | | |
|--|---------|--|-----|---------------------|---------------|
| Part Number | Price | Description | Qty | Drawing Link | Weight g [oz] |
| OPT2034 | \$1nx4: | Wenglor mounting bracket, right-angle, vertical adjustment, nickel plated steel. For use with OPT2024 & OPT2025 photoelectric sensors. | 1 | PDF | 38 [1.34] |



[OPT2034](#)

Right-angle Swivel Mounting Systems

Mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, 12mm rod mount. For use with OPT2024-OPT2025 photoelectric sensors. Available in all 304 stainless steel or with an aluminum mounting head and 304 stainless steel mounting plate.

| Accessories for 25mm Sensors | | | | | | |
|------------------------------|---------|---|---------------------|---------------------|---------------------|-------------|
| Part Number | Price | Description | Mounting Head | Mounting Plate | Drawing Link | Weight [lb] |
| OPT2124 | \$1nn4: | Wenglor mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, aluminum, 12mm rod mount. For use with OPT2024 & OPT2025 photoelectric sensors. | Aluminum | 304 Stainless Steel | PDF | 0.15 |
| OPT2125 | \$1nn5: | Wenglor mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, 304 stainless steel, 12mm rod mount. For use with OPT2024 & OPT2025 photoelectric sensors. | 304 Stainless Steel | 304 Stainless Steel | PDF | 0.27 |

Note: 304 Stainless steel mounting rods sold separately: [OPT2109](#) (200mm length), [OPT2110](#) (300mm length), and [OPT2111](#) (500mm length).



[OPT2124](#), [OPT2125](#)