



Pliers & Cutting Tools

GRIPLOCK® Pliers

CHANNELLOCK® GRIPLOCK pliers have an ergonomically designed offset head that provides more leverage. A special jaw design allows it to grip down on many shapes for added versatility. These pliers are built to last with a PERMALOCK® fastener to eliminate nut and bolt failure and laser-hardened teeth to provide a better, longer lasting grip. GRIPLOCK pliers are made in USA and forged from high-carbon U.S. steel that is specially coated for ultimate rust prevention.

Features

- Special GRIPLOCK jaw design
- Patented SAFE-T-STOP® feature prevents finger pinch
- Strong laser-hardened teeth for superior grip and longevity
- CHANNELLOCK BLUE® grips for comfort



GRIPLOCK Pliers						
Part Number	Part Image	Overall Length	Jaw Length	Jaw Capacity	Jaw Thickness	Price
<u>GL6</u>		6.5in (165mm)	1.00in (25.4mm)	1.06in (26.9mm)	0.25in (6.3mm)	\$-6hlt:
<u>GL10</u>		9.5in (241mm)	1.34in (34.0mm)	1.25in (31.8mm)	0.36in (9.1mm)	\$-6hlp:
<u>GL12</u>		12.5in (318mm)	1.77in (45.0mm)	2.25in (57.2mm)	0.48in (12.2mm)	\$-6hlp:

GRIPLOCK Pliers Sets			
Part Number	Part Image	Set Includes	Price
<u>GLS-3</u>		(3) Classic grip tongue and groove pliers (6.5In, 9.5In, and 12.5In)	\$-6hlt: