



Pliers & Cutting Tools

Long Nose Pliers

CHANNELLOCK® long nose pliers feature a crosshatch tooth pattern providing a maximum grip and a narrow nose profile that delivers extra precision in hard-to-reach areas. A precision-machined knife and anvil style cutting system ensures perfect mating while state-of-the-art laser heat treating offers a strong and consistent pattern across the cutting edge, adding increased strength and longevity over traditional hardening practices. CHANNELLOCK long nose pliers are made in the USA and forged from high-carbon U.S. steel that is specially coated for ultimate rust prevention.

Features

- Precise narrow nose design provides accessibility for hard-to-reach applications
- Laser heat-treated cutting edges perform better and last longer
- CHANNELLOCK BLUE® grips for comfort


Slip Joint Pliers


CHANNELLOCK® slip joint pliers are versatile and easy to use. They feature a serrated jaw for a firm grip and an added wire cutting shear for soft wire. CHANNELLOCK slip joint pliers are made in the USA and forged from high-carbon U.S. steel that is specially coated for ultimate rust prevention.

Features

- Two-position adjustment accommodates various sizes
- Serrated jaw and pipe grip design for a firm grip
- Reliable PERMALOCK® fastener eliminates nut and bolt failure with increased joint strength
- CHANNELLOCK BLUE® grips for comfort



Long Nose Pliers				
Part Number	Part Image			
317				
Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Price
8.0in (203mm)	2.36in (59.9mm)	0.87in (22.1mm)	0.41in (10.4mm)	\$--6hlj:

Slip Joint Pliers				
Part Number	Part Image			
526				
Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Price
6.5in (165mm)	0.96in (24.4mm)	1.28in (32.5mm)	0.43in (10.9mm)	\$-6hlk: