



Wrenches




Adjustable Wrenches


The CHANNELLOCK® adjustable wrenches feature non-protruding jaws for greater access in tight spaces. The combination of a smart and comfortable tapered handle design, precise four-thread knurl, and minimal head width improves performance in everyday use.

Features

- Measurement scales are laser engraved for sizing nuts, pipe, and tube diameters
- Precise four-thread knurl improved adjustment accuracy
- Non-protruding jaws allow access to hard-to-reach as
- Rugged chrome vanadium steel construction
- Chrome finish for ultimate rust prevention



Adjustable Wrenches						
Part Number	Part Image	Overall Length	Fastening Size	Jaw Thickness	Wrench Features	Price
804		4.5in (114mm)	0-1/2in	0.37in (9.5mm)	4-thread knurl adjuster laser engraved measurement scales	\$-6hlz:
806W		6.2in (157mm)	0-15/16in	0.43in (10.9mm)	Extra wide jaws 4-thread knurl adjuster laser engraved measurement scales	\$-6hlv:
808W		8.0in (203mm)	0-1 1/16in	0.55in (14.0mm)		\$-6hlx:
810W		10.0in (254mm)	0-1 5/16in	0.62in (15.7mm)		\$-6hly:

Adjustable Wrench Sets					
Part Number	Part Image	Contains	Description	Set Includes	Price
WS-2		806W 810W	CHANNELLOCK adjustable wrench set, 2 pieces, extra wide jaws, 4-thread knurl adjuster and laser engraved measurement scales.	(2) Chrome vanadium steel wide adjustable wrenches (0-15/16in capacity (806w), 0-1 5/16in capacity (810w))	\$-6hlz: