

iX7NH System Non-Brake Motor Power Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
APCS-PN03LSX-AD	\$,;5!lb:	N	3m [9.8 ft]		PDF	FBL/FCL series motors
APCS-PN05LSX-AD	\$,;5!lc:		5m [16.4 ft]		PDF	
APCS-PN10LSX-AD	\$,;5!ld:		10m [32.8 ft]		PDF	
APCS-PN20LSX-AD	\$,;05!le:		20m [65.6 ft]		PDF	
APCS-PF03LSX-AD	\$,;5!lf:	Y	3m [9.8 ft]		PDF	
APCS-PF05LSX-AD	\$,;5!lg:		5m [16.4 ft]		PDF	
APCS-PF10LSX-AD	\$,;05!lh:		10m [32.8 ft]		PDF	
APCS-PF20LSX-AD	\$,;05!li:		20m [65.6 ft]		PDF	
APCS-PN03HSX1-AD	\$,;5!lg:	N	3m [9.8 ft]		PDF	APM-FE15A series motors without brake
APCS-PN05HSX1-AD	\$,;5!la:		5m [16.4 ft]		PDF	
APCS-PN10HSX1-AD	\$,;5!lg:		10m [32.8 ft]		PDF	
APCS-PN20HSX1-AD	\$,;05!lh:		20m [65.6 ft]		PDF	
APCS-PF03HSX1-AD	\$,;-5!li:	Y	3m [9.8 ft]		PDF	
APCS-PF05HSX1-AD	\$,;-5!lj:		5m [16.4 ft]		PDF	
APCS-PF10HSX1-AD	\$,;05!lk:		10m [32.8 ft]		PDF	
APCS-PF20HSX1-AD	\$,;-05!ll:		20m [65.6 ft]		PDF	
APCS-PN03HSX-AD	\$,;5!ln:	N	3m [9.8 ft]		PDF	APM-FE16D and APM-FE22D series motors without brake
APCS-PN05HSX-AD	\$,;5!lo:		5m [16.4 ft]		PDF	
APCS-PN10HSX-AD	\$,;5!lp:		10m [32.8 ft]		PDF	
APCS-PN20HSX-AD	\$,;05!lq:		20m [65.6 ft]		PDF	
APCS-PF03HSX-AD	\$,;5!ls:	Y	3m [9.8 ft]		PDF	
APCS-PF05HSX-AD	\$,;5!lt:		5m [16.4 ft]		PDF	
APCS-PF10HSX-AD	\$,;05!lu:		10m [32.8 ft]		PDF	
APCS-PF20HSX-AD	\$,;05!lv:		20m [65.6 ft]		PDF	
APCS-PN03ISX-AD	\$,5!76:	N	3m [9.8 ft]		PDF	APM-FF35D motors without brake
APCS-PN05ISX-AD	\$,5!77:		5m [16.4 ft]		PDF	
APCS-PN10ISX-AD	\$,5!78:		10m [32.8 ft]		PDF	
APCS-PN20ISX-AD	\$,05!79:		20m [65.6 ft]		PDF	
APCS-PF03ISX-AD	\$,5!7a:	Y	3m [9.8 ft]		PDF	
APCS-PF05ISX-AD	\$,5!7b:		5m [16.4 ft]		PDF	
APCS-PF10ISX-AD	\$,05!7c:		10m [32.8 ft]		PDF	
APCS-PF20ISX-AD	\$,05!7d:		20m [65.6 ft]		PDF	

NOTE: These parts available for sale to North American locations only



APCS-PxxLSX series power cable



APCS-PxxHSX1 series power cable



APCS-PxxHSX series power cable

Accessories, continued

iX7NH System Brake Motor Power Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
Note: For FBL/FCL 100W–1kW motors with brake, use the power cables on the previous page AND separate brake cable APCS-BxxxQS-AD from page tSRV-82. This is for FBL/FCL motors only. FE and FF motors have brake wiring incorporated into the power cable (below).						
APCS-PN03NBX1-AD	\$,;5!x:	N	3m [9.8 ft]		PDF	APM-FE15A series motors with brakes
APCS-PN05NBX1-AD	\$,;5!y:		5m [16.4 ft]		PDF	
APCS-PN10NBX1-AD	\$,;05!z:		10m [32.8 ft]		PDF	
APCS-PN20NBX1-AD	\$,;05!!:		20m [65.6 ft]		PDF	
APCS-PF03NBX1-AD	\$,;5!![:	Y	3m [9.8 ft]		PDF	
APCS-PF05NBX1-AD	\$,;05!]:		5m [16.4 ft]		PDF	
APCS-PF10NBX1-AD	\$,;05!#:		10m [32.8 ft]		PDF	
APCS-PF20NBX1-AD	\$,;05!\$:		20m [65.6 ft]		PDF	
APCS-PN03NBX-AD	\$,;5!?:	N	3m [9.8 ft]		PDF	APM-FE16D and APM-FE22D series motors with brakes
APCS-PN05NBX-AD	\$,;5!,:		5m [16.4 ft]		PDF	
APCS-PN10NBX-AD	\$,;5!?:		10m [32.8 ft]		PDF	
APCS-PN20NBX-AD	\$,;05!?:		20m [65.6 ft]		PDF	
APCS-PF03NBX-AD	\$,;5!?:	Y	3m [9.8 ft]		PDF	
APCS-PF05NBX-AD	\$,;05!?:		5m [16.4 ft]		PDF	
APCS-PF10NBX-AD	\$,;05!?:		10m [32.8 ft]		PDF	
APCS-PF20NBX-AD	\$,;05!?:		20m [65.6 ft]		PDF	
APCS-PN03PBX-AD	\$,;5!e:	Y	3m [9.8 ft]		PDF	APM-FF35D series motors with brakes
APCS-PN05PBX-AD	\$,;5!f:		5m [16.4 ft]		PDF	
APCS-PN10PBX-AD	\$,;05!g:		10m [32.8 ft]		PDF	
APCS-PN20PBX-AD	\$,;05!h:		20m [65.6 ft]		PDF	
APCS-PF03PBX-AD	\$,;05!i:	N	3m [9.8 ft]		PDF	
APCS-PF05PBX-AD	\$,;05!j:		5m [16.4 ft]		PDF	
APCS-PF10PBX-AD	\$,;05!k:		10m [32.8 ft]		PDF	
APCS-PF20PBX-AD	\$,;05!l:		20m [65.6 ft]		PDF	



APCS-PxxNBX1 series power cable



APCS-PxxNBX series power cable



APCS-PxxPBX series power cable