



LS Electric AC Servo Systems

Accessories, *continued*

NOTE: These parts available for sale to North American locations only

L7C/L7P/iX7NH System Motor Brake Power Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
<u>APCS-BN03QS-AD</u>	\$;58]c:	N	3m [9.8 ft]	18AWG	<u>PDF</u>	APMC FBL/FCL brake motors (100W – 1kW)
<u>APCS-BN05QS-AD</u>	\$;58]d:		5m [16.4 ft]		<u>PDF</u>	
<u>APCS-BN10QS-AD</u>	\$;58]e:		10m [32.8 ft]		<u>PDF</u>	
<u>APCS-BN20QS-AD</u>	\$;58]f:		20m [65.6 ft]		<u>PDF</u>	
<u>APCS-BF03QS-AD</u>	\$;58]g:	Y	3m [9.8 ft]		<u>PDF</u>	
<u>APCS-BF05QS-AD</u>	\$;58]h:		5m [16.4 ft]		<u>PDF</u>	
<u>APCS-BF10QS-AD</u>	\$;58]i:		10m [32.8 ft]		<u>PDF</u>	
<u>APCS-BF20QS-AD</u>	\$;-058]j:		20m [65.6 ft]		<u>PDF</u>	



APCS-BN series brake cable

LS ELECTRIC L7C Series AC Servo Systems

Accessories, *continued*

NOTE: These parts available for sale to North American locations only

L7C System Motor Power Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
<u>APCS-PN03LSC-AD</u>	\$,58]1:	N	3m [9.8 ft]	18AWG	<u>PDF</u>	APMC FBL/FCL motors (100W – 1kW) used with L7C drives
<u>APCS-PN05LSC-AD</u>	\$,58]2:		5m [16.4 ft]		<u>PDF</u>	
<u>APCS-PN10LSC-AD</u>	\$,58]3:		10m [32.8 ft]		<u>PDF</u>	
<u>APCS-PN20LSC-AD</u>	\$,58]4:		20m [65.6 ft]		<u>PDF</u>	
<u>APCS-PF03LSC-AD</u>	\$,58]5:	Y	3m [9.8 ft]		<u>PDF</u>	
<u>APCS-PF05LSC-AD</u>	\$58z#:		5m [16.4 ft]		<u>PDF</u>	
<u>APCS-PF10LSC-AD</u>	\$,058zl:		10m [32.8 ft]		<u>PDF</u>	
<u>APCS-PF20LSC-AD</u>	\$058z?:		20m [65.6 ft]		<u>PDF</u>	



APCS-PN series motor cable

L7P System Non-Brake Motor Power Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
APCS-PN03LS-AD	\$-5i6f:	N	3m [9.8 ft]	18AWG	PDF	FBL/FCL series motors
APCS-PN05LS-AD	\$-5i6g:		5m [16.4 ft]		PDF	
APCS-PN10LS-AD	\$-5i6h:		10m [32.8 ft]		PDF	
APCS-PN20LS-AD	\$-5i6i:		20m [65.6 ft]		PDF	
APCS-PF03LS-AD	\$-5i6j:	Y	3m [9.8 ft]		PDF	
APCS-PF05LS-AD	\$-5i6k:		5m [16.4 ft]		PDF	
APCS-PF10LS-AD	\$-05i6l:		10m [32.8 ft]		PDF	
APCS-PF20LS-AD	\$-05i6n:		20m [65.6 ft]		PDF	
APCS-PN03HS-AD	\$-5i6o:	N	3m [9.8 ft]	14AWG	PDF	APM-FE series motors without brake
APCS-PN05HS-AD	\$-5i6p:		5m [16.4 ft]		PDF	
APCS-PN10HS-AD	\$-5i6q:		10m [32.8 ft]		PDF	
APCS-PN20HS-AD	\$-05i6s:		20m [65.6 ft]		PDF	
APCS-PF03HS-AD	\$-5i6t:	Y	3m [9.8 ft]		PDF	
APCS-PF05HS-AD	\$-5i6u:		5m [16.4 ft]		PDF	
APCS-PF10HS-AD	\$-05i6v:		10m [32.8 ft]		PDF	
APCS-PF20HS-AD	\$-05i6x:		20m [65.6 ft]		PDF	
APCS-PN03IS-AD	\$-5i6_:	N	3m [9.8 ft]	14AWG	PDF	230VAC APM-FF35D and 460VAC APM-FFP35D motors without brakes
APCS-PN05IS-AD	\$-5i6#:		5m [16.4 ft]		PDF	
APCS-PN10IS-AD	\$-05i6l:		10m [32.8 ft]		PDF	
APCS-PN20IS-AD	\$-05i6?:		20m [65.6 ft]		PDF	
APCS-PF03IS-AD	\$-5i6,::	Y	3m [9.8 ft]		PDF	
APCS-PF05IS-AD	\$-5i70:		5m [16.4 ft]		PDF	
APCS-PF10IS-AD	\$-05i71:		10m [32.8 ft]		PDF	
APCS-PF20IS-AD	\$-05i72:		20m [65.6 ft]		PDF	
APCS-PN03JS-AD	\$-5i77:	N	3m [9.8 ft]	10AWG	PDF	230VAC APM-FF55D motors without brake
APCS-PN05JS-AD	\$-5i78:		5m [16.4 ft]		PDF	
APCS-PN10JS-AD	\$-05i79:		10m [32.8 ft]		PDF	
APCS-PN20JS-AD	\$-05i7a:		20m [65.6 ft]		PDF	
APCS-PF03JS-AD	\$-5i7b:	Y	3m [9.8 ft]		PDF	
APCS-PF05JS-AD	\$-05i7c:		5m [16.4 ft]		PDF	
APCS-PF10JS-AD	\$-05i7d:		10m [32.8 ft]		PDF	
APCS-PF20JS-AD	\$-05i7e:		20m [65.6 ft]		PDF	
APCS-PF03JS1-AD	\$5nn5:	Y	3m [9.8 ft]	12AWG	PDF	460VAC APM-FFP55D and APM-FFP75D motors without brakes
APCS-PF05JS1-AD	\$05nn6:		5m [16.4 ft]		PDF	
APCS-PF10JS1-AD	\$05nn7:		10m [32.8 ft]		PDF	
APCS-PF20JS1-AD	\$05nn8:		20m [65.6 ft]		PDF	
APCS-PN03JS2-AD	\$05nnd:	N	3m [9.8 ft]	8AWG	PDF	230VAC APM-FF75D motors without brake
APCS-PN05JS2-AD	\$05nne:		5m [16.4 ft]		PDF	
APCS-PN10JS2-AD	\$05nnf:		10m [32.8 ft]		PDF	
APCS-PN20JS2-AD	\$05nng:		20m [65.6 ft]		PDF	
APCS-PF03JS2-AD	\$05nnh:	Y	3m [9.8 ft]		PDF	
APCS-PF05JS2-AD	\$-05nni:		5m [16.4 ft]		PDF	
APCS-PF10JS2-AD	\$-05nnj:		10m [32.8 ft]		PDF	
APCS-PF20JS2-AD	\$05nnk:		20m [65.6 ft]		PDF	

NOTE: These parts available for sale to North American locations only



APCS-PxxLS series power cable



APCS-PxxHS series power cable



APCS-PxxIS series power cable



APCS-PxxJS series power cable

Accessories, continued

L7P System Brake Motor Power Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
Note: For FBL/FCL 100W-1kW motors with brake, use the power cables on page tMNC-234 (APCS-PxxxLS-AD) AND separate brake cable APCS-BxxxQS-AD from page tMNC-232. This is for FBL/FCL motors only. FE and FF motors have brake wiring incorporated into the power cable (below).						
APCS-PN03NB-AD	\$--5i7j:	N	3m [9.8 ft]	14AWG	PDF	230VAC and 460 VAC APM-FE series motors with brakes
APCS-PN05NB-AD	\$-5i7k:		5m [16.4 ft]		PDF	
APCS-PN10NB-AD	\$--5i7l:		10m [32.8 ft]		PDF	
APCS-PN20NB-AD	\$-05i7n:		20m [65.6 ft]		PDF	
APCS-PF03NB-AD	\$-5i7o:	Y	3m [9.8 ft]		PDF	
APCS-PF05NB-AD	\$-05i7p:		5m [16.4 ft]		PDF	
APCS-PF10NB-AD	\$-05i7q:		10m [32.8 ft]		PDF	
APCS-PF20NB-AD	\$-05i7s:		20m [65.6 ft]		PDF	
APCS-PN03PB-AD	\$-5i7y:	N	3m [9.8 ft]		PDF	230VAC APM-FF35D and 460VAC APM-FFP35D motors with brakes
APCS-PN05PB-AD	\$-5i7z:		5m [16.4 ft]		PDF	
APCS-PN10PB-AD	\$;-05i7j:		10m [32.8 ft]		PDF	
APCS-PN20PB-AD	\$;-05i7l:		20m [65.6 ft]		PDF	
APCS-PF03PB-AD	\$-05i7_:	Y	3m [9.8 ft]		PDF	
APCS-PF05PB-AD	\$-05i7#:		5m [16.4 ft]		PDF	
APCS-PF10PB-AD	\$;-05i7l:		10m [32.8 ft]		PDF	
APCS-PF20PB-AD	\$-05i7?:		20m [65.6 ft]		PDF	
APCS-PN03LB-AD	\$-5i83:	N	3m [9.8 ft]	8AWG	PDF	230VAC APM-FF55D motors with brake
APCS-PN05LB-AD	\$-5i84:		5m [16.4 ft]		PDF	
APCS-PN10LB-AD	\$-05i85:		10m [32.8 ft]		PDF	
APCS-PN20LB-AD	\$-05i86:		20m [65.6 ft]		PDF	
APCS-PF03LB-AD	\$-05i87:	Y	3m [9.8 ft]		PDF	
APCS-PF05LB-AD	\$-05i88:		5m [16.4 ft]		PDF	
APCS-PF10LB-AD	\$-05i89:		10m [32.8 ft]		PDF	
APCS-PF20LB-AD	\$-05i8a:		20m [65.6 ft]		PDF	
APCS-PF03LB1-AD	\$5nn9:	Y	3m [9.8 ft]	12AWG	PDF	460VAC APM-FFP55D and APM-FFP75D motors with brakes
APCS-PF05LB1-AD	\$05nna:		5m [16.4 ft]		PDF	
APCS-PF10LB1-AD	\$05nnb:		10m [32.8 ft]		PDF	
APCS-PF20LB1-AD	\$05nnc:		20m [65.6 ft]		PDF	
APCS-PN03LB2-AD	\$-05nnl:	N	3m [9.8 ft]	8AWG	PDF	230VAC APM-FF75D motors with brake
APCS-PN05LB2-AD	\$05nnn:		5m [16.4 ft]		PDF	
APCS-PN10LB2-AD	\$05nno:		10m [32.8 ft]		PDF	
APCS-PN20LB2-AD	\$05nnp:		20m [65.6 ft]		PDF	
APCS-PF03LB2-AD	\$05nnq:	Y	3m [9.8 ft]		PDF	
APCS-PF05LB2-AD	\$05nns:		5m [16.4 ft]		PDF	
APCS-PF10LB2-AD	\$;05nnt:		10m [32.8 ft]		PDF	
APCS-PF20LB2-AD	\$05nnu:		20m [65.6 ft]		PDF	



APCS-PxxNB series power cable



APCS-PxxPB series power cable



APCS-PxxLB series power cable