

Multi-Wire Connectors Accessories

Crimp Contacts - 10 and 16 Amp

Crimp contacts are made of hard silver-plated alloy. Wires to be connected must be carefully matched with the correct wire size of crimp contacts. Crimp contacts should be installed using a crimping tool.

10 Amp Crimp Contacts - 100/Pack

Male	Price	Weight g [oz]	Female	Price	Weight g [oz]	Wire Gauge mm ² [AWG]	Stripping Length
<u>14104164</u>	\$;6hkt:	71.67 [2.53]	<u>14103164</u>	\$-6hkl:	68.95 [2.43]	0.14-0.37 [26-22]	8mm [0.31in]
<u>14104264</u>	\$6hku:	70.31 [2.48]	<u>14103264</u>	\$6hkn:	68.49 [2.42]	0.5 [20]	
<u>14104364</u>	\$6hkv:	67.59 [2.38]	<u>14103364</u>	\$6hko:	67.13 [2.37]	0.75 [18]	
<u>14104564</u>	\$6hky:	66.23 [2.34]	<u>14103564</u>	\$6hkq:	66.68 [2.35]	1.5 [16]	
<u>14104664</u>	\$6hkz:	61.60 [2.17]	<u>14103664</u>	\$6hks:	62.60 [2.21]	2.5 [14]	



Male Crimp Contact



Female Crimp Contact



Male Crimp Contact



Female Crimp Contact

16 Amp Crimp Contacts - 100/Pack

Male	Price	Weight g [oz]	Female	Price	Weight g [oz]	Wire Gauge mm ² [AWG]	Stripping Length
<u>14106164</u>	\$-6hl1:	120.43 [4.25]	<u>14105164</u>	\$;6hk]:	156.95 [5.54]	0.14-0.37 [26-22]	7.5mm [0.29in]
<u>14106264</u>	\$-6hl2:	135.17 [4.77]	<u>14105264</u>	\$;6hk[:	162.84 [5.74]	0.5 [20]	
<u>14106364</u>	\$-6hl3:	131.09 [4.62]	<u>14105364</u>	\$6hk_:	146.51 [5.17]	0.75 [18]	
<u>14106564</u>	\$-6hl5:	131.32 [4.63]	<u>14105564</u>	\$;6hkl:	152.86 [5.39]	1.5 [16]	
<u>14106664</u>	\$-6hl6:	139.71 [4.93]	<u>14105664</u>	\$6hk?:	166.47 [5.87]	2.5 [14]	
<u>14106864</u>	\$-6hl8:	136.53 [4.82]	<u>14105864</u>	\$-6hl0:	154.68 [5.46]	4.0 [12]	

Crimp Contact Tools

Part Number	Price	Qty	Description	Weight [lb]
<u>ZP-MC-CT1</u>	\$007qg:	1	Crimping tool w/die set and locator	1.593
<u>ZP-MC-CT2</u>	\$007qh:		Crimping tool w/die set only, no locator	0.814
<u>ZP-MC-RT1</u>	\$007s3:		Removal tool for 10A contacts	0.081
<u>ZP-MC-RT2</u>	\$007s4:		Removal tool for 16A contacts	0.086



[ZP-MC-CT1](#)



[ZP-MC-CT2](#)



[ZP-MC-RT1](#)



[ZP-MC-RT2](#)