



Hose Clamps

**HC-58**

NITRA Adjustable Hose Clamps				
Part No.	Description	Pcs/Pkg	Weight (lbs)	Price
<u>HC-316</u>	NITRA hose clamp, 2-ear, 0.318-0.433in diameter, plated steel. For use with HBV series 3/16in hose.	10	0.1	\$11#s:
<u>HC-516</u>	NITRA hose clamp, 2-ear, 0.492-0.591in diameter, plated steel. For use with HBV series 5/16in hose.	10	0.1	\$11#u:
<u>HC-38</u>	NITRA hose clamp, 2-ear, 0.551-0.669in diameter, plated steel. For use with HBV series 3/8in hose.	10	0.1	\$11#v:
<u>HC-12</u>	NITRA hose clamp, 2-ear, 0.638-0.787in diameter, plated steel. For use with HBV series 1/2in hose.	10	0.1	\$11#x:
<u>HC-58</u>	NITRA hose clamp, 2-ear, 0.748-0.906in diameter, plated steel. For use with HBV series 5/8in hose.	10	0.2	\$11#y:
<u>HC-34</u>	NITRA hose clamp, 2-ear, 0.945-1.102in diameter, plated steel. For use with HBV series 3/4in hose.	10	0.3	\$11#z:
<u>HC-1</u>	NITRA hose clamp, 2-ear, 1.154-1.339in diameter, plated steel. For use with HBV series 1in hose.	10	0.3	Retired

**HCSS-58**

NITRA Interlocking Hose Clamps				
Part No.	Description	Pcs/Pkg	Weight (lbs)	Price
<u>HCSS-316</u>	NITRA hose clamp, interlocking ear, 0.346-0.413in diameter, 304 stainless steel. For use with HBV series 3/16in hose.	10	0.1	\$;11#[:
<u>HCSS-14</u>	NITRA hose clamp, interlocking ear, 0.398-0.465in diameter, 304 stainless steel. For use with HBV series 1/4in hose.	10	0.1	\$11#_:
<u>HCSS-516</u>	NITRA hose clamp, interlocking ear, 0.472-0.571in diameter, 304 stainless steel. For use with HBV series 5/16in hose.	10	0.1	\$11##:
<u>HCSS-38</u>	NITRA hose clamp, interlocking ear, 0.520-0.618in diameter, 304 stainless steel. For use with HBV series 3/8in hose.	10	0.1	\$;11#[:
<u>HCSS-12</u>	NITRA hose clamp, interlocking ear, 0.654-0.780in diameter, 304 stainless steel. For use with HBV series 1/2in hose.	10	0.1	\$11#?:
<u>HCSS-58</u>	NITRA hose clamp, interlocking ear, 0.823-0.949in diameter, 304 stainless steel. For use with HBV series 5/8in hose.	10	0.1	\$;11#,:
<u>HCSS-34</u>	NITRA hose clamp, interlocking ear, 0.941-1.067in diameter, 304 stainless steel. For use with HBV series 3/4in hose.	10	0.1	\$;11!0:
<u>HCSS-1</u>	NITRA hose clamp, interlocking ear, 1.236-1.362in diameter, 304 stainless steel. For use with HBV series 1in hose.	10	0.1	\$;11!1:



Hose Crimping Tools

NITRA hose crimping tools are designed to work with 2-ear and interlocking ear hose clamps. They come in three styles.

- Straight jaw single action, straight jaw compound action and side jaw compound action styles available
- Made in USA



HCT-ES



HCT-SC

Nitra Hose Crimping Tools

Part Number	Description	Pcs/Pkg	Package Weight (lbs)	Price
<u>HCT-ES</u>	NITRA hose clamp crimping tool, single action, straight jaw	1	0.8	\$;11!2:
<u>HCT-SC</u>	NITRA hose clamp crimping tool, compound action, straight jaw	1	0.9	\$;11!3:

