

Accessories, continued

NOTE: These parts available for sale to North American locations only

PHOX System Motor Encoder Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
APCV-EN03ES1-AD	\$0675#:	N	3m [9.8 ft]	24AWG	PDF	All PHOX APMC motors
APCV-EN05ES1-AD	\$,0675!:		5m [16.4 ft]		PDF	
APCV-EN10ES1-AD	\$0675?:		10m [32.8 ft]		PDF	
APCV-EN20ES1-AD	\$,0675.:		20m [65.6 ft]		PDF	
APCV-EF03ES1-AD	\$06760:	Y	3m [9.8 ft]		PDF	
APCV-EF05ES1-AD	\$06761:		5m [16.4 ft]		PDF	
APCV-EF10ES1-AD	\$06762:		10m [32.8 ft]		PDF	
APCV-EF20ES1-AD	\$06763:		20m [65.6 ft]		PDF	



APCV-EN series encoder cable

PHOX System Motor Power Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
APCV-PN03LS-AD	\$675u:	N	3m [9.8 ft]	24AWG	PDF	All PHOX APMC motors
APCV-PN05LS-AD	\$675v:		5m [16.4 ft]		PDF	
APCV-PN10LS-AD	\$675x:		10m [32.8 ft]		PDF	
APCV-PN20LS-AD	\$0675y:		20m [65.6 ft]		PDF	
APCV-PF03LS-AD	\$675z:	Y	3m [9.8 ft]		PDF	
APCV-PF05LS-AD	\$,675]:		5m [16.4 ft]		PDF	
APCV-PF10LS-AD	\$,0675[:		10m [32.8 ft]		PDF	
APCV-PF20LS-AD	\$0675.:		20m [65.6 ft]		PDF	



APCV-PN series power cable

PHOX System Motor Brake Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
APCV-BN03QS-AD	\$6764:	N	3m [9.8 ft]	24AWG	PDF	All PHOX APMC motors
APCV-BN05QS-AD	\$6765:		5m [16.4 ft]		PDF	
APCV-BN10QS-AD	\$6766:		10m [32.8 ft]		PDF	
APCV-BN20QS-AD	\$6767:		20m [65.6 ft]		PDF	
APCV-BF03QS-AD	\$6768:	Y	3m [9.8 ft]		PDF	
APCV-BF05QS-AD	\$6769:		5m [16.4 ft]		PDF	
APCV-BF10QS-AD	\$676a:		10m [32.8 ft]		PDF	
APCV-BF20QS-AD	\$0676b:		20m [65.6 ft]		PDF	



APCV-BN series brake cable

Note: Each brake cable consists of 4 wires: 24VDC and Common (input to the drive), and BRK+ and BRK- output to the motor brake.