

Seifert Fan Hoods



Features

- Protects fan and exhaust vents from environmental hazards.
- Screw-less mounting and removal of the hood.
- Easy to clean.
- Mounting screws torque: 40 lb-in / 4.5 Nm.
- cULus Recognized File E498756.
- IP56



Stainless Steel Hood

- 304 stainless steel
- Blue Food Safe Gasket
- UL Type 1,2,3,3X,3R,3RX,3S,3SX,5,12,12K and 13



Seifert Stainless Steel Fan Hood				
Part Number	Price	Max Cutout Size	Max Covered Area	Drawing Link
400000020	\$-05i3z:	3.62 x 3.62 [91.95 x 91.95]	4.19 x 4.19 [106.43 x 106.43]	PDF
400010020	\$;-05i3]:	4.92 x 4.92 [124.97 x 124.97]	5.91 x 5.91 [150.11 x 150.11]	PDF
400020020	\$;-05i3[:	6.97 x 6.97 [177.04 x 177.04]	8.03 x 8.03 [203.96 x 203.96]	PDF
400030020	\$-05i3_:	8.78 x 8.78 [223.01 x 223.01]	9.84 x 9.84 [249.94 x 249.94]	PDF
400040020	\$-05i3#:	11.46 x 11.46 [291.08 x 291.08]	12.80 x 12.80 [325.12 x 325.12]	PDF

NOTE: Dimensions listed as inches [millimeters]

Carbon Steel Hood

- Carbon steel, powder coated RAL 7035 light gray
- UL Type 1,2,5,12,12K and 13



Seifert Carbon Steel Fan Hood				
Part Number	Price	Max Cutout Size	Max Covered Area	Drawing Link
4000000200	\$;-5i3!:	3.62 x 3.62 [91.95 x 91.95]	4.19 x 4.19 [106.43 x 106.43]	PDF
4000100200	\$-05i3?:	4.92 x 4.92 [124.97 x 124.97]	5.91 x 5.91 [150.11 x 150.11]	PDF
4000200200	\$;-05i3,:	6.97 x 6.97 [177.04 x 177.04]	8.03 x 8.03 [203.96 x 203.96]	PDF
4000300200	\$-05i40:	8.78 x 8.78 [223.01 x 223.01]	9.84 x 9.84 [249.94 x 249.94]	PDF
4000400200	\$-05i41:	11.46 x 11.46 [291.08 x 291.08]	12.80 x 12.80 [325.12 x 325.12]	PDF

NOTE: Dimensions listed as inches [millimeters]