


SPARTAN
 SCIENTIFIC

3825 Series Valves


 Part no. [3825-66-B20Y-A](#)

 Part no. [3825-66-B20G-A](#)

3825 series valves are 2-way, normally closed, direct acting valves. The engineered composite body material and other wetted materials are suitable for potable water applications.

Features

- Direct acting operator
- Glass reinforced Nylon body
- Port size 1/4 push to connect tubing
- 2-way, 2-position normally closed operation
- 24 VDC or 120 VAC (other voltage coils available)



See our website
www.AutomationDirect.com
 for a variety of cable options.

3825 Series Solenoid Valves										
Part No.	Price	Ports	Cv	Max Pressure	Operating Voltage	Connection	Weight (lbs)	Drawing Link	Vendor Specs	Vendor Application and Install Guide
3825-66-B20Y-A	\$,5x[t:	1/4in push-to-connect tubing inlet(s), 1/4in push-to-connect tubing outlet(s)	0.24	150 psi	120VAC	11mm DIN style wiring plug	0.23	PDF	PDF	PDF
3825-66-B20U-A	\$,5x[u:				24VDC		0.23	PDF		
3825-67-B20Y-A	\$,5x[z:		0.31	75 psi	120VAC	18mm DIN style wiring plug	0.23	PDF		
3825-67-B20U-A	\$,5x[[:			60 psi	24VDC		0.23	PDF		
3825-66-B20G-A	\$,5x[[:		0.24	150 psi	120VAC	18in pigtail (PVC 22AWG multi-strand copper wire 300 Volt)	0.23	PDF		
3825-66-B20C-A	\$,5x[_:				24VDC		0.23	PDF		
3825-67-B20G-A	\$,5x[#:		0.31	75 psi	120VAC		0.23	PDF		
3825-67-B20C-A	\$,5x[!:			60 psi	24VDC		0.23	PDF		