

Stride[®] Managed Industrial Ethernet Switches

Industrial Hardened Full Feature Layer 2 Switch



• For detailed specifications on all models, see following pages

<i>SE Series</i>		
Price		
starting at \$005dd: (5 port)		
Full Feature Layer 2 Switch		
✓		
Industrial Temperature Ranges		
	Wide Temp	-40 to +75°C
Ethernet Connectivity		
	RJ45 Ports	up to 1000 Mbps
	Fiber Optic Ports	✓
	SFP Ports	✓
Port Count		
5,8,10,16		
Industrial Protocol Management		
	Modbus TCP	Read
	EtherNet/IP	—
Network Redundancy		
	STP/RSTP	✓
	Proprietary Fast Recovery	Real-Time Ring
Mounting		
	DIN Rail Mount	✓
	Panel Mount	Integrated
Input Power		
	Redundant Power Inputs	✓
	Reverse Polarity Protection	✓
	Power LED	✓
	Power Alarm	✓
Agency Approvals		
	UL508 / 61010	✓
	Haz Loc—Class 1 Div 2	✓
	ATEX Zone 2	✓
	CE	✓
Warranty		
5 years		