



# Wera Ratchets & Sockets

BE A TOOL REBEL



## Zyklon Metal Ratchet



### Small return angle

The fine 72 tooth ratchet mechanism has a low return angle of 5°. This short stroke allows fast and precise work in small spaces.



### Extremely slim Long leverage

Forged, chrome-molybdenum steel ratchet has no torque limitation and is designed to fit in tight areas.



### Secure socket lock mechanism

The ball lock holds sockets and attachments securely, ensuring safe operation. To release the socket simply press the release button.

Wera Metal Ratchets			
Part Number	Description	Pcs/ Pkg	Price
<a href="#"><u>05004004055</u></a>	Wera Zyklon Metal ratchet, switch lever, 1/4in drive, 5 degrees return angle, all-metal construction, ballpoint socket locking mechanism.	1	\$11k1:
<a href="#"><u>05004034055</u></a>	Wera Zyklon Metal ratchet, switch lever, 3/8in drive, 5 degrees return angle, all-metal construction, ballpoint socket locking mechanism.	1	\$11k2:
<a href="#"><u>05004064055</u></a>	Wera Zyklon Metal ratchet, switch lever, 1/2in drive, 5 degrees return angle, all-metal construction, ballpoint socket locking mechanism.	1	\$11k3:



### Switch Lever

Switch lever for convenient change of direction.

# Wera Ratchets & Sockets

## Zyklop Metal 1/2in Drive Ratchet and Socket Sets



Zyklop Metal 1/2in Drive Ratchet and Socket Sets			
05004081055		05004078055	
Wera Zyklop Metal standard ratchet, driver bit, and socket set, Phillips, internal hex, Torx and external hex, 28 pieces, 1in bit length, 1/2in drive, imperial.		Wera Zyklop Metal standard ratchet, driver bit, and socket set, Phillips, internal hex, Torx and external hex, 28 pieces, 1in bit length, 1/2in drive, metric.	
\$;011kf:		\$011ke:	
Type	Size	Type	Size
Zyklop Metal ratchet	1/2in	Zyklop Metal ratchet	1/2in
Extension	1/2in x 250mm	Extension	1/2in x 250mm
Wobble extension	1/2in x 52mm	Wobble extension	1/2in x 52mm
Bit adaptor	1/2in x 5/16in x 50mm	Bit adaptor	1/2in x 5/16in x 50mm
	6-point socket 37mm long		6-point socket 37mm long
	External hex bit, 30mm long		External bit, 30mm long
	Phillips bit 32mm long		Phillips bit 32mm long
	Torx bit, 35mm long		Torx bit 35mm long
	3/8, 7/16, 1/2, 9/16, 19/32, 5/8, 11/16, 3/4, 25/32, 13/16in		10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm
	7/32, 1/4, 5/16, 3/8in		5, 6, 8, 10mm
	#2, #3		#2, #3
	T20, T25, T27, T30, T40, T45, T50, T55		T20, T25, T27, T30, T40, T45, T50, T55

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.