



Wera Ratchets & Sockets

BE A TOOL REBEL



Zyklon Metal Ratchet



Small return angle

The fine 72 tooth ratchet mechanism has a low return angle of 5°. This short stroke allows fast and precise work in small spaces.



Extremely slim Long leverage

Forged, chrome-molybdenum steel ratchet has no torque limitation and is designed to fit in tight areas.



Secure socket lock mechanism

The ball lock holds sockets and attachments securely, ensuring safe operation. To release the socket simply press the release button.

Wera Metal Ratchets			
Part Number	Description	Pcs/Pkg	Price
<u>05004004055</u>	Wera Zyklon Metal ratchet, switch lever, 1/4in drive, 5 degrees return angle, all-metal construction, ballpoint socket locking mechanism.	1	\$11k1:
<u>05004034055</u>	Wera Zyklon Metal ratchet, switch lever, 3/8in drive, 5 degrees return angle, all-metal construction, ballpoint socket locking mechanism.	1	\$11k2:
<u>05004064055</u>	Wera Zyklon Metal ratchet, switch lever, 1/2in drive, 5 degrees return angle, all-metal construction, ballpoint socket locking mechanism.	1	\$11k3:















Switch Lever

Switch lever for convenient change of direction.

Wera Ratchets & Sockets

Zyklop Metal 1/4in Drive Ratchet and Socket Sets



Zyklop Metal 1/4in Drive Ratchet and Socket Sets					
05004021055			05004018055		
					
Wera Zyklop Metal standard ratchet, driver bit, and socket set, Phillips, Pozidriv, internal hex, Torx and external hex, 28 pieces, 1in bit length, 1/4in drive, imperial.			\$011kb:		Wera Zyklop Metal standard ratchet, driver bit, and socket set, Phillips, Pozidriv, internal hex, Torx and external hex, 28 pieces, 1in bit length, 1/4in drive, metric.
Type		Size	Type		Size
Zyklop metal ratchet		1/4in	Zyklop metal ratchet		1/4in
Extension		1/4in x 150mm	Extension		1/4in x 150mm
Wobble extension		1/4in x 56mm	Wobble extension		1/4in x 56mm
Bit adapter		1/4in x 37mm	Bit adapter		1/4in x 37mm
	6-point socket 23mm long	3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2in		6-point socket 23mm long	5, 5.5, 6, 7, 8, 10, 11, 12, 13mm
	External hex bit, 25mm long	3, 4, 5, 6mm		External hex bit, 25mm long	3, 4, 5, 6mm
	Phillips bit 25mm long	#1, #2, #3		Phillips bit 25mm long	#1, #2, #3
	Posidriv bit 25mm long	#1, #2		Posidriv bit 25mm long	#1, #2
	Torx bit 25mm long	T10, T15, T20, T25, T27, T30		Torx bit, 25mm long	T10, T15, T20, T25, T27, T30

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.