



Wera Wrenches

Insulated Adjustable Wrenches

Wera Joker VDE insulated adjustable wrenches are Individually tested tools as per IEC 60900 at 10,000 V for safe working at the approved voltage of 1,000V. The adjustable VDE spanner continuously and automatically grips all hexagonal sizes in the indicated range of dimensions - metric and imperial. The integrated lever mechanism securely clamps the hexagon screw or bolt between the jaws, which significantly reduces the risk of slippage or damage. The ratchet feature ensures fast and consistent screwdriving without removing the tool. The single-arm design, in conjunction with the ratchet feature and the corner-width prism, makes it possible to work even in confined spaces. Safety is increased by the anti-slip protection at the front end of the handle. The sliding function offers contactless and safe opening of the non-insulated jaws, thereby providing extra protection.



Features

- Individually tested with insulated handles for safe working up to 1,000 volt, with anti-slip protection and sliding function for contactless and safe opening of the non-insulated jaws
- Automatic and continuous grip of hexagon screws and bolts
- Lever mechanism when gripping avoids slipping and damage
- Fast and consistent screwdriving without removing the wrench thanks to mechanical ratchet function
- Return angle of only 30° through placement in the corner-width rectangular prisms in the mouth



Insulated Adjustable Wrenches						
Part Number	Wrench Type	Fastening Size	Jaw Thickness	Overall Length	Wrench Features	Price
<u>05020150001</u>	Adjustable	1/4-3/8in	0.30in (7.7mm)	4.7in (119mm)	Automatic and continuous self-setting, 30 degree low return angle, and contactless jaw opening feature	\$6266:
<u>05020151001</u>		7/16-1/2in	0.39in (10.0mm)	6.1in (155mm)		\$6267:
<u>05020152001</u>		1/2-5/8in	0.49in (12.4mm)	7.5in (190mm)		\$6268:
<u>05020153001</u>		5/8-3/4in	0.55in (14.0mm)	8.9in (226mm)		\$6269:

Insulated Adjustable Wrench Sets				
Part Number	Number of Pieces	Part Image	Set Includes	Price
<u>05020170001</u>	4		(4) Joker VDE adjustable wrenches (1/4-3/8in capacity, 7/16-1/2in capacity, 1/2-5/8in capacity, 5/8-3/4in capacity)	\$626a: