

Wera Screwdrivers

Insulated Screwdrivers





As with all other Wera tools, safety is a top priority for series 100 VDE screwdrivers. All Wera insulated screwdrivers are individually tested at 10,000V, in accordance with IEC 60900, ensuring safe working up to 1,000V. The quality of the blades exceeds current standards with respect to hardness and torque strength.




Insulated Screwdrivers									
Part Number	Part Image	Type	Tip Size	Overall Length	Shaft Length	Shaft Diameter	Reduced Shank	Handle Length	Price
<u>05006440055*</u>		Slotted	3.5mm	7.1in (180mm)	3.9in (100mm)	0.14in (3.5mm)	Yes	3.2in (81mm)	\$11hs:
<u>05006441055*</u>			4.0mm	7.8in (198mm)		0.20in (5.1mm)		3.9in (99mm)	\$;11ht:
<u>05006442055*</u>			5.5mm	8.8in (223mm)	4.9in (125mm)	0.24in (6.1mm)			\$11hu:
<u>TW-SD-VSL-1</u>			2.5mm	8.7in (220mm)	3.1in (80mm)	0.20in (5.1mm)	No	3.2in (81mm)	\$cok:
<u>TW-SD-VSL-2</u>			3.0mm	9.4in (240mm)	3.9in (100mm)	0.12in (3.0mm)			\$;cpt:
<u>TW-SD-VSL-3</u>			4.0mm	10.0in (255mm)		0.24in (6.1mm)		3.9in (99mm)	\$cpv:
<u>TW-SD-VSL-4</u>			5.5mm	11.0in (280mm)	4.9in (125mm)	0.22in (5.6mm)			\$0cpv:

*Does not have a Lasertip laser-etched non-slip tip.



Insulated Screwdrivers - Cont'd									
Part Number	Part Image	Type	Tip Size	Overall Length	Shaft Length	Shaft Diameter	Reduced Shank	Handle Length	Price
<u>05006450055*</u>		⊕ Phillips	#1	7.0in (177mm)	3.1in (80mm)	0.16in (4.0mm)	Yes	3.9in (99mm)	\$11hv:
<u>05006451055*</u>			#2	8.1in (205mm)	3.9in (100mm)	0.24in (6.1mm)		4.1in (104mm)	\$11hx:
<u>TW-SD-VPH-1*</u>			#1	9.3in (236mm)	3.1in (80mm)	0.16in (4.0mm)		3.2in (81mm)	\$-coi:
<u>TW-SD-VPH-2</u>			#2	8.1in (205mm)	3.9in (100mm)	0.24in (6.1mm)	No	4.1in (104mm)	\$-0coj:

*Does not have a Lasertip laser-etched non-slip tip.

Insulated Screwdriver Sets						
Part Number	Number of Pieces	Part Image	Type	Tip Size	Set Includes	Price
<u>TW-SD-SET-2</u>	6		⊕ Phillips	#1 #2	(4) insulated slotted screwdrivers (2.5, 3.5, 4, 5.5mm), (2) insulated Phillips screwdrivers (#1, #2), wall mount rack	\$;0cof:
			⊖ Slotted	2.5mm 3.5mm 4.0mm 5.5mm		