



Ratcheting T-Handles

Wera’s ratcheting t-handle is an integrated ratchet with fine toothing (80 teeth/return angle 4.5°) that eases and accelerates screwdriving without having to reposition the tool. The ratchet mechanism completely embedded in the handle ensures very handy and comfortable work. With reversing lever for comfortable clockwise/counterclockwise direction change in one-handed operation. The ergonomic shape of the handle fills the ball of the hand well, while the fingers lie securely in the softly rounded recessed grips. The whole hand comes into contact with the handle which avoids friction loss between the hand and handle.

Features

- The integrated ratchet with fine toothing ensures fast and safe working
- Reversing lever for comfortable clockwise/counterclockwise direction change
- Convenient operation thanks to the ratchet mechanism fully embedded in the handle
- Ergonomic 2-component handle with finger handle recesses and pleasant surface feel for very high power transmission and fatigue-free working
- Fast-rotating sleeve for extremely high working speed
- 1/4" socket mounting with secure ball lock or bitholder with 1/4 in external hexagon drive as per DIN ISO 1173-C 6.3 and E 6.3



Ratcheting T-Handles					
Part Number	Part Image	Lock Mechanism	Shaft Length	Handle Type	Price
05023460001		Ballpoint socket	1.8in (45mm)	Ergonomic t-handle	\$626o:
05023461001		Rapidaptor quick-release bit holder			\$626p:



Ratcheting T-Handle Sets						
Part Number	Number of Pieces	Part Image	Type	TipSize	Set Includes	Price
<u>05023471001</u>	17		Phillips	#2 #3	(1) 1/4in t-handle ratchet bitholding screwdriver with Rapidaptor quick-release chuck, (16) 3.5 driver bits (Phillips: #2, #3 Pozidriv: #2, #3, torx: T10, T15, T20, T25, T30, T40, hex: 3mm, 4mm, 5mm, 6mm, 8mm, slotted: 5.5mm), (1) textile storage pouch	-\$0626i:
			Pozidriv	#2 #3		
			Torx	T10 T15 T20 T25 T30 T40		
			External Hex	3mm 4mm 5mm 6mm 8mm		
			Slotted	5.5mm		
<u>05057473001</u>	17		Phillips	#2 #3	(1) 1/4in t-handle ratchet bitholding screwdriver with Rapidaptor quick-release chuck, (16) 3.5 driver bits (Phillips: #2, #3, torx: T10, T15, T20, T25, T30, T40, hex: 1/8in, 5/32in, 3/16in, 7/32in, 1/4in, square: #2, #3, slotted: 5.5mm), (1) textile storage pouch	-\$0626q:
			Pozidriv	#2 #3		
			Torx	T10 T15 T20 T25 T30 T40		
			External Hex	1/8in 5/32in 3/16in 7/32in 1/4in		
			Slotted	5.5mm		