



Wera Screwdrivers

Standard Screwdrivers

Wera Kraftform Plus standard screwdrivers transfer more torque with less effort, relieving physical stress even during intensive use. Combined with other practical and technical product advantages, such as the lasertip for a secure fit in the screw, and greater cam-out protection, Kraftform screwdrivers are the perfect choice for manual work.



Standard Screwdrivers									
Part Number	Part Image	Type	Tip Size	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Price
<u>TW-SD-SL-1</u>		 Slotted	3.0mm	6.3in (160mm)	3.1in (80mm)	0.12in (3.0mm)	3.2in (81mm)	Kraftform ergonomic handle	\$;cp,:
<u>TW-SD-SL-2</u>			4.0mm	7.8in (198mm)	3.9in (100mm)	0.16in (4.0mm)	3.9in (99mm)		\$cq0:
<u>TW-SD-SL-3</u>			5.5mm	8.8in (223mm)	4.9in (125mm)	0.22in (5.6mm)			\$cq1:
<u>TW-SD-SL-4</u>			6.5mm	12.4in (315mm)	5.9in (150mm)	0.26in (6.5mm)	4.1in (104mm)		\$0cq2:
<u>05008027055*</u>			4.0mm	10.0in (255mm)	11.8in (300mm)	0.16in (4.0mm)	3.9in (99mm)		\$11hy:
<u>05008060055*</u>			5.5mm	11.0in (280mm)	11.8in (300mm)	0.24in (6.1mm)			\$11hz:
<u>TW-SD-PH-1</u>		 Phillips	#1	9.4in (240mm)	3.1in (80mm)	0.12in (3.0mm)	4.1in (104mm)		\$cp_:
<u>TW-SD-PH-2</u>			#2	10.6in (269mm)	3.9in (100mm)	0.20in (5.1mm)			\$0cp#:
<u>TW-SD-PH-3*</u>			#0	5.6in (141mm)	2.4in (60mm)	0.12in (3.0mm)		3.2in (81mm)	\$;cp :
<u>05008730055</u>			#2	15.9in (405mm)	11.8in (300mm)	0.24in (6.1mm)		4.1in (104mm)	\$;11h[:

*Includes a hardened Black Point tip instead of laser-etched non-slip tip.



Standard Screwdrivers - Cont'd									
Part Number	Part Image	Type	Tip Size	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Price
<u>05023105001</u>		 External hex	2.0mm	5.7in (145mm)	3.0in (75mm)	0.12in (3.0mm)	2.8in (70mm)	Kraftform ergonomic handle	\$626g:
<u>05023107001</u>			2.5mm	6.1in (156mm)			3.2in (81mm)		\$626h:
<u>05023110001</u>			3.0mm			0.16in (4.0mm)			\$-626i:
<u>05138262055*</u>		 Tamperproof torx	TX20	7.8in (198mm)	3.9in (100mm)	0.18in (4.6mm)	3.9in (99mm)		

*Includes a hardened Black Point tip instead of laser-etched non-slip tip.

Standard Screwdriver Sets						
Part Number	Number of Pieces	Part Image	Type	Tip Size	Set Includes	Price
<u>TW-SD-SET-1</u>	6		+ Phillips — Slotted	#1 #2 3.0mm 4.0mm 5.5mm 6.5mm	(4) slotted screwdrivers (3, 4, 5.5, 6.5mm), (2) Phillips screwdrivers (#1, #2), wall mount rack	\$0cp?: