



Signal Devices

Visual 29mm Beacons With Permanent LED Indicator

Features

- High-intensity LED permanent beacon
- Mounting for either 22.5 mm panel mount or M20 thread for use with limit and cable-operated switches
- Lock nut included with 22.5 mm models
- Mostly sideways illumination
- Rubber seal included
- 2-year warranty



Visual 29mm Beacons With Permanent LED Indicator Selection Chart

Part Number	Price	LED Color	Drawing Link	Description	Voltage	Current	Starting Current	Operating Temp /Protection	Life Duration	Housing Material	Weight g[oz]	Connection	Agency Approvals
230 Series 20mm x 1.5 Threaded Base													
23010055	\$-0c#i:	Red	PDF	LED Permanent Light	24VDC	< 45mA	≤ 0.5 A	-4 to 122°F [-20 to 50°C] IP65	up to 100,000h	Polycarbonate cap ABS/ Polycarbonate blend, Black base	12 [0.42]	M20 x 1.5 20.5 mm Threaded base Does not include lock nut 2 wires, approximately 115mm long 20AWG (0.5 mm ²)	cULus file E164155, CE, RoHS
23020055	\$00c#k:	Green	PDF										
23030055	\$0c#n:	Yellow	PDF										
23040055	\$0c#p:	Clear	PDF										
23050055	\$0c#s:	Blue	PDF										
23010067	\$-0c#j:	Red	PDF		115VAC	< 15mA	–						
23020067	\$-00c#l:	Green	PDF										
23030067	\$0c#o:	Yellow	PDF										
23040067	\$00c#q:	Clear	PDF										
23050067	\$;00c#t:	Blue	PDF										
231 Series 22.5 mm Panel Mount													
23110055	\$;0c!q:	Red	PDF	LED Permanent Light	24VDC	< 45mA	≤ 0.5 A	-4 to 122°F [-20 to 50°C] IP65	up to 100,000h	Polycarbonate cap ABS/ Polycarbonate blend, Black base	16 [0.56]	M22 x 1.5 22.5 mm Panel mount 2 wires, approximately 105mm long 20AWG (0.5 mm ²)	cULus file E164155, CE, RoHS
23120055	\$;00c!t:	Green	PDF										
23130055	\$;0c!v:	Yellow	PDF										
23140055	\$;00c!y:	Clear	PDF										
23150055	\$;0c!j:	Blue	PDF										
23110067	\$;0c!s:	Red	PDF		115VAC	< 15mA	–						
23120067	\$;00c!u:	Green	PDF										
23130067	\$;0c!x:	Yellow	PDF										
23140067	\$;00c!z:	Clear	PDF										
23150067	\$;00c![:	Blue	PDF										

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.