

KS 71 Pre-assembled Stacklights



**64924001 and
64924002**

KombiSIGN 71 Pre-assembled Stacklights Features

- Available in common voltages of 24 VAC/VDC and 115VAC
- IP65
- LED Permanent Optical Elements
- 70mm diameter/base mount models
- Polycarbonate lens material
- Polyamide glass fiber-reinforced terminal element with cage clamp (part number [64080000](#))

KS 71 Pre-assembled Stacklights									
Part Number	Price	Drawing Link	Voltage	Colors	Current	Starting Current	Operating Temp	Life Duration	Weight g [oz]
64924001	\$00?ab:	PDF	115VAC	Green, yellow, red	max. 20mA	–	-20 to 50°C [-4 to 122°F]	Up to 100,000h	249 [8.78]
64924002	\$00?ac:	PDF	24 VAC/VDC		max. 25mA	max. 500mA			
64924003	\$00?ad:	PDF	115VAC	Green, red	max. 20mA	–			191 [6.74]
64924004	\$00?ae:	PDF	24 VAC/VDC		max. 25mA	max. 500mA			



**64924003 and
64924004**

Components for KS 71 Pre-assembled Stacklights				
Image				
Part Number	97584001	97584085	97584086	96000002
Price	\$;04?h:	\$05hb:	\$05hc:	\$05h9:
Drawing Link	PDF	PDF	PDF	PDF
General Description	Contact box with side cable exit, with mounting material	Bracket for 1-sided mounting, including rubber seals	Bracket for 2-sided mounting, including rubber seals	Bracket for surface mounting with cable gland

Configuring Your KombiSIGN 71 Stack Light

STEP 1

Select the required optical elements for your application

STEP 2

Select the optional audible elements for your application



Optical Signal Elements

- Incandescent Permanent Light
- LED Permanent Light
- LED Flashing Light
- LED Blinking Light
- LED Rotating Light
- Xenon Flashing Light

Audible Signal Elements

- Buzzer Element
- Siren Element

Plain Base Mount

Tube Base Mount

STEP 3

Select the correct terminal element for your mounting option (includes cap)



Plain Base Mount


- Screw terminal
Order no. [64082000](#)
- CAGE CLAMP® terminal
Order no. [64080000](#)

Tube Base Mount

- Screw terminal
Order no. [64083000](#)
- CAGE CLAMP® terminal
Order no. [64081000](#)

STEP 4

Where appropriate, select a base and the desired tube length (only for tube mounting)



Plain Base Mount

- Tube with clamp
Order no. [96000018](#)
- Adapter for single hole mounting
Order no. [96000025](#)
- Base with integrated tube
Order no. [97584010](#)

Tube Base Mount

- Tube Ø 25 mm, all anodized
Order no. [97584510](#)
100 mm long [97584025](#)
250 mm long [97584040](#)
400 mm long [97584060](#)
600 mm long [97584080](#)
800 mm long [97584090](#)
1000 mm long [97584003](#)
- Base for Tube, plastic
Order no. [97584090](#)
- Base for Tube, metal
Order no. [97584091](#)
- Foldaway Base
Order no. [96000030](#)
- Tube Ø 25 mm, plastic, only for Foldaway Base, 45 mm long
Order no. [96000031](#)

STEP 5

Where appropriate, select the bracket and the contact box.



Plain Base Mount

- Contact box with side cable exit
Order no. [97584001](#)
- Bracket for base mounting
Order no. [96000002](#)
- Bracket for 1-sided mounting
Order no. [97584085](#)
- Bracket for 2-sided mounting
Order no. [97584086](#)

Tube Base Mount

- Contact box with side cable exit
Order no. [97584001](#)
- Contact box with magnetic base and side cable exit
Order no. [97584004](#)
- Bracket for base mounting with concealed cable entry
Order no. [96000014](#)
- Bracket for tube mounting
Order no. [96000001](#)