







Insulated Nutdriver Sets

Wiha Insulated SoftFinish® Cushion Grip screwdrivers consist of Wiha engineered premium quality tool steel for strength and durability, have black oxide finish for corrosion protection, and feature exact fit precision machined tips for reduced cam-out. All Wiha Insulated screwdrivers are VDE Certified and meet EN/IEC 60900 testing standards for protection against arc flash explosion, ASTM F1505 standard specifications for insulated and insulating hand tools, NFPA-70E standards for elec safety on the jobsite, and CSA testing benchmarks for safety and performance. SoftFinish® driver handles feature an 8-edged large-diameter comfort grip for maximum gripping area, giving the user powerful torque and less fatigue.



Features

- Ergonomic cushion grip handle for comfort and control
- Dual durometer construction for long-lasting durability
- Handle directly molded to the blade for permanent bond
- Handle size proportionate to blade for consistent mechanical advantage
- Parallel flats for roll-off prevention
- Tip profile labeled on cap for easy identification
- Wiha premium quality tool steel for strength and durability
- Black oxide finish for corrosion protection
- Exact fit precision machined tip for reduced cam-out
- Individually tested to 10,000 volts AC and rated to 1,000 volts AC for safety and peace of mind

Insulated Nutdriver Sets							
Part Number	Number of Pieces	Part Image	Type	Tip Size	Insulation Rating	Set Includes	Price
<u>WT32293</u>	7		 Internal Hex	5.0mm 6.0mm 7.0mm 8.0mm 9.0mm 10.0mm 11.0mm 12.0mm 13.0mm		(7) insulated SoftFinish nut drivers (5.0mm, 6.0mm, 7.0mm, 8.0mm, 9.0mm, 10.0mm, 11.0mm, 12.0mm, 13.0mm)	\$68pv:
<u>WT32294</u>	7		 Internal Hex	3/16in 7/32in 1/4in 5/16in 3/8in 7/16in 1/2in		(7) insulated SoftFinish nut drivers (3/16in, 7/32in, 1/4in, 5/16in, 3/8in, 7/16in, 1/2in)	\$68px: