

# wiha Screwdrivers

Tools that work for you










## Precision Screwdrivers

Wiha Precision Screwdrivers feature cushion-grip handles for comfort and control, and the dual durometer material is direct molded to the blade for a permanent bond. The Precision style includes a hex profile finger grip for precise torque and a tapered handle for rapid rotation. The handles are sized proportionate to the tip and feature an extra-long handle with a smooth-turning cap for multiple hand positions. The driver tip profiles are labeled on the handle to quickly and easily identify the driver.
















## Features

- Handle direct molded to blade for a permanent bond
- Tapered handle for rapid rotation
- Extra-long handle for optimal hand positions and smooth turning
- Tip profile labeled on handle for easy identification
- Handle sized proportionate to the blade for consistent mechanical advantage
- Wiha engineered premium quality tool steel for strength and durability
- Chrome-plated satin finish for corrosion protection
- Exact fit precision machined tip for reduced cam-out

Precision Screwdrivers															
Part Number	Part Image	Type	Tip Size	Slotted Tip Thickness	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Price					
<a href="#"><u>WT26008</u></a>		 Slotted	0.8mm	0.16mm	4.7in (119mm)	1.6in (40mm)	0.08in (2.0mm)	3.1in (79mm)	Cushion grip handle with rotating cap	\$61u5:					
<a href="#"><u>WT26010</u></a>			1.0mm	0.18mm						\$61u6:					
<a href="#"><u>WT26012</u></a>			1.2mm	0.2mm						\$61u7:					
<a href="#"><u>WT26015</u></a>			1.5mm	0.25mm						\$61u0:					
<a href="#"><u>WT26018</u></a>			1.8mm	0.3mm	2.0mm	0.4mm	5.7in (145mm)	2.0in (50mm)		\$61u1:					
<a href="#"><u>WT26020</u></a>			2.0mm	0.4mm						\$61u2:					
<a href="#"><u>WT26022</u></a>										\$61u3:					
<a href="#"><u>WT26023</u></a>										\$61u4:					








# wiha Screwdrivers

Tools that work for you

Precision Screwdrivers - Cont'd											
Part Number	Part Image	Type	Tip Size	Slotted Tip Thickness	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Price	
<a href="#"><u>WT26025</u></a>		 Slotted	2.5mm	0.4mm	5.7in (145mm)	2.0in (50mm)	0.10in (2.5mm)	3.7in (94mm)	Cushion grip handle with rotating cap	\$61ua:	
<a href="#"><u>WT26027</u></a>					7.7in (196mm)	3.9in (100mm)		3.8in (97mm)		\$61ub:	
<a href="#"><u>WT26028</u></a>					9.6in (243mm)	5.9in (150mm)		3.7in (94mm)		\$68ns:	
<a href="#"><u>WT26030</u></a>			3.0mm	0.5mm	5.7in (145mm)	2.0in (50mm)	0.12in (3.0mm)	3.7in (94mm)		\$61uc:	
<a href="#"><u>WT26032</u></a>					6.7in (170mm)	2.4in (60mm)		4.3in (109mm)		\$61ud:	
<a href="#"><u>WT26033</u></a>					8.3in (211mm)	3.9in (100mm)		4.4in (112mm)		\$61ue:	
<a href="#"><u>WT26034</u></a>					10.2in (259mm)	5.9in (150mm)		4.4in (112mm)		\$;61uf:	
<a href="#"><u>WT26035</u></a>			3.5mm	0.6mm	6.7in (170mm)	2.4in (60mm)	0.14in (3.5mm)	4.3in (109mm)		\$61ug:	
<a href="#"><u>WT26040</u></a>			4.0mm	0.8mm			0.16in (4.0mm)			4.3in (109mm)	\$61uh:
<a href="#"><u>WT26041</u></a>					8.3in (211mm)	3.9in (100mm)	4.4in (112mm)	\$;68nt:			
<a href="#"><u>WT26042</u></a>					10.2in (259mm)	5.9in (150mm)	4.3in (109mm)	\$68n_:			
<a href="#"><u>WT26074</u></a>			3.5mm	0.6mm	6.3in (160mm)	2.4in (60mm)	0.14in (3.5mm)	3.9in (99mm)		\$-61ui:	















Tools that work for you

Precision Screwdrivers - Cont'd										
Part Number	Part Image	Type	Tip Size	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Price	
<a href="#"><u>WT26102</u></a>		⊕ Phillips	#000	4.7in (119mm)	1.6in (40mm)	0.08in (2.0mm)	3.1in (79mm)	Cushion grip handle with rotating cap	\$-61ul:	
<a href="#"><u>WT26100</u></a>			#00						\$-61uj:	
<a href="#"><u>WT26105</u></a>			#0	5.7in (145mm)	2.0in (50mm)	0.12in (3.0mm)	3.7in (94mm)		\$61un:	
<a href="#"><u>WT26108</u></a>				6.7in (170mm)	3.0in (75mm)				\$61uo:	
<a href="#"><u>WT26109</u></a>				9.6in (243mm)	5.9in (150mm)				\$.68n[:	
<a href="#"><u>WT26110</u></a>			#1	6.7in (170mm)	2.4in (60mm)	0.16in (4.0mm)	4.3in (109mm)		\$61up:	
<a href="#"><u>WT26115</u></a>				10.2in (259mm)	5.9in (150mm)				\$68o0:	



Tools that work for you

Precision Screwdrivers - Cont'd									
Part Number	Part Image	Type	Tip Size	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Price
<a href="#"><u>WT26307</u></a>		 External Hex	0.7mm (.028in)	4.7in (119mm)	1.6in (40mm)	0.10in (2.5mm)	3.1in (79mm)	Cushion grip handle with rotating cap	\$68o1:
<a href="#"><u>WT26309</u></a>			0.9mm (.035in)						\$68o2:
<a href="#"><u>WT26313</u></a>			1.3mm (.050in)						\$61us:
<a href="#"><u>WT26315</u></a>			1.5mm	5.7in (145mm)	2.0in (50mm)	0.09in (2.3mm)	3.7in (94mm)		\$,61ut:
<a href="#"><u>WT26316</u></a>			1/16in						\$68o3:
<a href="#"><u>WT26320</u></a>			2.0mm (5/64in)						\$61uu:
<a href="#"><u>WT26323</u></a>			3/32in	6.7in (170mm)	2.4in (60mm)	0.11in (2.9mm)	4.3in (109mm)		\$68o4:
<a href="#"><u>WT26325</u></a>			2.5mm						\$61uv:
<a href="#"><u>WT26326</u></a>			7/64in			0.12in (3.0mm)			\$68o5:
<a href="#"><u>WT26334</u></a>			3mm			0.14in (3.5mm)			\$68o9:
<a href="#"><u>WT26335</u></a>			1/8in			0.15in (3.8mm)			\$68oa:

# wiha Screwdrivers

Tools that work for you



















## Precision Screwdriver Sets









Wiha Precision Screwdrivers feature cushion-grip handles for comfort and control, and the dual durometer material is direct-molded to the blade for a permanent bond. The precision style includes a hex profile finger grip for precise torque and a tapered handle for rapid rotation. The handles are sized proportionate to the tip and feature an extra-long handle with a smooth-turning cap for multiple hand positions.

## Features

- Handle direct molded to blade for a permanent bond
- Tapered handle for rapid rotation
- Extra-long handle for optimal hand positions and smooth turning
- Tip profile labeled on handle for easy identification
- Handle sized proportionate to the blade for consistent mechanical advantage
- Wiha engineered premium quality tool steel for strength and durability
- Chrome-plated satin finish for corrosion protection
- Exact fit precision machined tip for reduced cam-out



Precision Screwdriver Sets						
Part Number	Number of Pieces	Part Image	Type	Tip Size	Set Includes	Price
<a href="#"><u>WT26090</u></a>	6		 Slotted	1.5mm 2mm 2.5mm 3mm 3.5mm 4mm	(6) precision screwdrivers (slotted: (1.5mm, 2.0mm, 2.5mm, 3.0mm, 3.5mm, 4.0mm))	\$68ny:
<a href="#"><u>WT26092</u></a>	7		 Phillips  Slotted	#0 2.5mm 3mm 4mm	(7) precision screwdrivers (slotted: (2.5 x 50mm, 2.5, 3.0, 4.0 x 100mm, 3.0, 4.0 x 150mm), Phillips (#0 x 75mm))	\$68nz:
<a href="#"><u>WT26098</u></a>	8		 Slotted	1mm 1.2mm 1.5mm 2mm 2.5mm 3mm 3.5mm 4mm	(8) precision screwdrivers (slotted: (1.0mm, 1.2mm, 1.5mm, 2.0mm, 2.5mm, 3.0mm, 3.5mm, 4.0mm)), canvas pouch.	\$.68n]:
<a href="#"><u>WT26192</u></a>	5		 Phillips  Slotted	#0 #1 2.5mm 3.0mm 4.0mm	(5) precision screwdrivers (slotted: (2.5mm, 3.0mm, 4.0mm), Phillips: (#0, #1))	\$68n#:
<a href="#"><u>WT26194</u></a>	4		 Phillips	#000 #00 #0 #1	(4) precision screwdrivers (Phillips: (#000, #00, #0, #1))	\$.68n!:
<a href="#"><u>WT26197</u></a>	7		 Phillips  Slotted	#00 #0 #1 1.5mm 2.0mm 2.5mm 3.0mm	(7) precision screwdrivers (Phillips: (#00, #0, #1), slotted (1.5mm, 2.0mm, 2.5mm, 3.0mm))	\$68n?:
<a href="#"><u>WT26199</u></a>	8		 Phillips  Slotted	#000 #00 #0 #1 1.0mm 2.0mm 3.0mm 4.0mm	(8) precision screwdrivers (slotted: (1.0mm, 2.0mm, 3.0mm, 4.0mm), Phillips: (#000, #00, #0, #1)), canvas pouch	\$.68n.:

Precision Screwdriver - Cont'd						
Part Number	Number of Pieces	Part Image	Type	Tip Size	Set Includes	Price
<a href="#"><u>WT26390</u></a>	7		 External Hex	0.7mm 0.9mm 1.3mm 1.5mm 2mm 2.5mm 3mm	(7) precision screwdrivers (hex: (0.7mm, 0.9mm, 1.3mm, 1.5mm, 2.0mm, 2.5mm, 3.0mm))	\$68o6:
<a href="#"><u>WT26391</u></a>	8			0.028in 0.035in 0.050in 1/16in 5/64in 3/32in 7/64in 1/8in	(8) precision screwdrivers (hex: (0.028in, 0.035in, 0.050in, 1/16in, 5/64in, 3/32in, 7/64in, 1/8in))	\$68o7:
<a href="#"><u>WT26491</u></a>	5		 Ball-end Hex	1.35mm 1.5mm 2mm 2.5mm 3mm	(5) precision screwdrivers (ball end hex: (1.35mm, 1.5mm, 2.0mm, 2.5mm, 3.0mm))	\$68o8:
<a href="#"><u>WT26791</u></a>	8		 Torx	T1 T2 T3 T4 T5 T6 T7 T8	(8) precision screwdrivers (torx: (T1, T2, T3, T4, T5, T6, T7, T8))	\$68od:
<a href="#"><u>WT26799</u></a>	8			T3 T4 T5 T6 T7 T8 T9 T10	(8) precision screwdrivers (torx: (T3, T4, T5, T6, T7, T8, T9, T10)), roll up pouch	\$68oe: