

# wiha Screwdrivers

Tools that work for you







## Drive-Loc Screwdrivers

Wiha SoftFinish® Drive-Loc Screwdrivers are some of the most versatile screwdrivers on the planet. The Drive-Loc system allows for professionals to continuously adjust shaft length. Short or long, Drive-Loc is built for any application. The Drive-Loc system quickly locks in place in 1/8 in increments, allowing for unprecedented flexibility.










## Features

- SoftFinish® cushion grip handle for comfort and control
- Drive-Loc VI features adjustable/reversible locking blades
- Blades made of high-performance CRM-72 tool steel
- 8-edged soft-grip maximizes turn force for 40% more power
- Selectable lengths (1.7 in – 4.8 in) in 1/8 in increments
- Tip profile labeled on cap for easy identification

**WT28188**

Drive-Loc Sets						
Part Number	Number of Pieces	Part Image	Type	Tip Size	Set Includes	Price
<b>WT28188</b>	32		 Phillips	#0 #1 #2	(1) SoftFinish Drive-Loc VI handle, (17) Drive-Loc VI adjustable/reversible blades (Phillips (#0, #1, #2), slotted (3.0mm, 3.5mm, 4.0mm, 4.5mm, 5.5mm, 6.0mm, 6.5mm), square (#1, #2), Tamperproof Torx T6, T7, T8, T9, T10, T15, T20, T25, T30, T40), hex (3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in, 2.0mm, 2.5mm, 3.0mm, 4.0mm, 5.0mm, 6.0mm), (14) Drive-Loc VI adjustable nut drivers (1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 7/16in, 1/2in, 5.5mm, 6.0mm, 7.0mm, 8.0mm, 9.0mm, 10.0mm, 11.0mm), 38 Position Wiha red and black wallet	\$068og:
			 Slotted	3.0mm 3.5mm 4.0mm 4.5mm 5.5mm 6.0mm 6.5mm		
			 Tamperproof Torx	T6 T7 T8 T9 T10 T15 T20 T25 T30 T40		
			 Square	#1 #2		
			 Internal Hex	1/4in 9/32in 5/16in 11/32in 3/8in 7/16in 1/2in 5.5mm 6.0mm 7.0mm 8.0mm 9.0mm 10.0mm 11.0mm		

## Drive-Loc Sets - Cont'd

Part Number	Number of Pieces	Part Image	Type	Tip Size	Set Includes	Price
<b><u>WT28189</u></b>	15		 Phillips	#1 #2	(1) SoftFinish Drive-Loc VI handle, (14) Drive-Loc VI adjustable/reversible blades (slotted (3.5mm, 4.5mm, 5.5mm, 6.5mm), Phillips (#1, #2), tamperproof torx (T6, T7, T8, T9, T10, T15, T20, T25, T30, T40), hex (2.0mm, 2.5mm, 3.0mm, 4.0mm, 5.0mm, 6.0mm, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in), (1) cushion grip blade lock handle in canvas pouch	\$068oh:
			 Slotted	3.5mm 4.5mm 5.5mm 6.5mm		
			 Tamperproof Torx	T6 T7 T8 T9 T10 T15 T20 T25 T30 T40		
			 External Hex	3/32in 7/64in 1/8in 9/64in 5/32in 3/16in 2.0mm 2.5mm 3.0mm 4.0mm 5.0mm 6.0mm		
<b><u>WT28196</u></b>	8		 Internal Hex	3/16in 1/4in 5/16in 11/32in 3/8in 7/16in 1/2in	(1) SoftFinish Drive-Loc VI handle, (7) Drive-Loc VI adjustable nut setters (3/16in, 1/4in, 5/16in, 11/32in, 3/8in, 7/16in, 1/2in), (1) cushion grip blade lock handle in canvas pouch	\$-68oi:
<b><u>WT28198</u></b>	8		 Internal Hex	5.0mm 5.5mm 6.0mm 7.0mm 8.0mm 9.0mm 10.0mm	(1) SoftFinish Drive-Loc VI handle, (7) Drive-Loc VI adjustable nut setters (5.0mm, 5.5mm, 6.0mm, 7.0mm, 8.0mm, 9.0mm, 10.0mm), (1) cushion grip blade lock handle in canvas pouch	\$-68oj: