




IBOCO® Spiral Wrap / Braided Sleeve



Dimensions



| Part Number | | Dimensions in Inches | | | Wire Bundle Size in Inches | Feet per Carton |
|--------------|------------------------------|----------------------|------|------|----------------------------|-----------------|
| Polyethylene | Flame-Retardant Polyethylene | A | B | C | | |
| P-1 | PA1 | 0.06 | 0.12 | 0.20 | 1/16 to 1/2 | 160 |
| P-2 | PA2 | 0.16 | 0.24 | 0.31 | 1/4 to 2 | 80 |
| P-3 | PA3 | 0.31 | 0.39 | 0.47 | 3/8 to 3 | 80 |
| P-4 | PA4 | 0.35 | 0.47 | 0.47 | 1/2 to 4 | 65 |

Spiral Wrap

For neatly grouping wire bundles simply and economically, spiral wrap has no equal. Strong, yet easy to install, it protects the wire bundle, keeping it flexible though tightly contained. It is easily removed and reusable for temporary wiring.

SPIRALITE Spiral Wrap Selection Chart

| Part Number | Price | Description | Color | Length |
|-------------|----------|--|---------|--------------|
| P-1 | \$-0814: | 0.12" nominal o.d. Polyethylene spiral wrap used for wire bundles from 1/16 to 1/2 inch diameter. | Natural | 160 ft./pack |
| PA1 | \$-0818: | 0.12" nominal o.d. self-extinguishing Polyethylene spiral wrap used for wire bundles from 1/16 to 1/2 inch diameter. | White | 160 ft./pack |
| P-2 | \$-0815: | 0.25" nominal o.d. Polyethylene spiral wrap used for wire bundles from 1/4 to 2 inch diameter. | Natural | 80 ft./pack |
| PA2 | \$-0819: | 0.25" nominal o.d. self-extinguishing Polyethylene spiral wrap used for wire bundles from 1/4 to 2 inch diameter. | White | 80 ft./pack |
| P-3 | \$-0816: | 0.37" nominal o.d. Polyethylene spiral wrap used for wire bundles from 3/8 to 3 inch diameter. | Natural | 80 ft./pack |
| PA3 | \$-081a: | 0.37" nominal o.d. self-extinguishing Polyethylene spiral wrap used for wire bundles from 3/8 to 3 inch diameter. | White | 80 ft./pack |
| P-4 | \$-0817: | 0.5" nominal o.d. Polyethylene spiral wrap used for wire bundles from 1/2 to 4 inch diameter. | Natural | 65 ft./pack |
| PA4 | \$-081b: | 0.5" nominal o.d. self-extinguishing Polyethylene spiral wrap used for wire bundles from 1/2 to 4 inch diameter. | White | 65 ft./pack |



Braided Sleeve Material Specifications

| | |
|----------------------------|---------------------------------|
| Operating Temp | -50 to +150°C [-58 to +302°F] |
| Physical Properties | Self-extinguishing for UL 94V-2 |
| Maximum Elongation | 42% |
| Diameter Expansion | 100% |
| Other | Halogen-free |

Braided Sleeve

This lightweight, expandable, self-extinguishing polyester sleeving has an open weave to allow maximum diameter expansion. It is super-flexible and easy to install, gripping objects of various shapes and sizes reliably. Abrasion-resistant, it provides extra protection against chemicals and flames.

Braided Sleeve Selection Chart

| Part Number | Price | Description | Color | Length |
|--------------|-----------|--|-------|--------------|
| TY-5 | \$008kz: | Braided expandable polyester sleeving, 0.19 in [5mm] nominal i.d., 0.15 in [4mm] to 0.47 in [12mm] nominal range | Black | 325 ft./pack |
| TY-10 | \$008kv: | Braided expandable polyester sleeving, 0.37 in [10mm] nominal i.d., 0.31 in [8mm] to 0.86 in [22mm] nominal range | Black | 325 ft./pack |
| TY-20 | \$008kx: | Braided expandable polyester sleeving, 0.75 in [20mm] nominal i.d., 0.63 in [16mm] to 1.37 in [35mm] nominal range | Black | 164 ft./pack |
| TY-30 | \$008ky: | Braided expandable polyester sleeving, 1.12 in [30mm] nominal i.d., 0.98 in [25mm] to 1.89 in [48mm] nominal range | Black | 164 ft./pack |
| TY-50 | \$;008kj: | Braided expandable polyester sleeving, 2.0 in [50mm] nominal i.d., 1.57 in [40mm] to 2.82 in [72mm] nominal range | Black | 164 ft./pack |