

# Motors & Gearboxes

in stock and ready to ship!



**MTR Series**  
starting at  
**\$86.00 U.S.**  
MTR-P33-1AB18  
1/3 HP

**Worm Gearboxes**  
starting at  
**\$130.00 U.S.**  
WG-175-xxx-x

**MTC Series**  
starting at  
**\$108.00 U.S.**  
MTC-001-3BD18  
1 HP



AutomationDirect's IronHorse™ line of general purpose motors and gearboxes comes from a manufacturer who has nearly three decades of solid experience and reliability in the North American motor market. When you combine that with our great pricing, same-day shipping\* and award-winning service, you have a winning combination!

- 56C Frame Rolled Steel Motors**  
0.33 to 2 hp, single-phase, 115/208-230 Volt  
0.33 to 2 hp, three-phase, 208-230/460 Volt
- Electrically reversible
  - Industrial gauge steel motor frame, TEFC enclosure

- T Frame Cast Iron Industrial Duty Motors**  
1 to 300 hp, three-phase, 208-230/460 Volt
- High efficiency
  - All cast iron frames, TEFC enclosure
  - Electrically reversible

- Worm Gearboxes utilize C-face mounting interfaces for C-face electric motors**
- 2.62, 2.37, 2.06 and 1.75 inch center distances available
  - Gear ratios include 5:1, 10:1, 15:1, 20:1, 40:1, and 60:1
  - Right-hand and dual output shafts
  - NEMA 56C and 182TC frame sizes
  - One-year warranty



- FREE award-winning Technical support
- Same-day shipping (cut off times vary by product; see Web site for details)
- FREE shipping on orders over \$300, shipped standard ground or LTL\*

**CHECK OUT PRICES ON MOTORS AND WORM GEARBOXES**

56C Framed Rolled Steel (MTR)	AutomationDirect IronHorse Price/Part Number
Single-phase, 115/208-230 Volt 0.5 hp, TEFC enclosure	<b>\$89.00</b> MTR-P50-1AB18
Three-phase, 208-230/460 Volt 2 hp, TEFC Enclosure	<b>\$148.00</b> MTR-002-3BD18
<b>T Frame Cast Iron (MTC)</b>	
Industrial Duty three-phase, TEFC enclosure, EPACT rated 2 hp 208-230/460 Volt	<b>\$137.00</b> MTC-002-3BD18
Industrial Duty three-phase, TEFC enclosure, EPACT rated 50 hp 460 Volt	<b>\$1,275.00</b> MTR-050-3D18
<b>Worm Gearboxes</b>	
Ratio 10:1 nominal 1.0 hp input, 1.75 inch center distance, dual shaft	<b>\$130.00</b> WG-175-010-D
Ratio 60:1 nominal 0.75 hp input, 2.62 inch center distance, right-hand shaft	<b>\$215.00</b> WG-262-060-R

AutomationDirect prices are U.S. published prices as of August 2008. Prices subject to change without notice.

[www.automationdirect.com](http://www.automationdirect.com)

For complete information or to order online, visit:  
[www.automationdirect.com/motors](http://www.automationdirect.com/motors) or  
[www.automationdirect.com/worm-gearboxes](http://www.automationdirect.com/worm-gearboxes)

**1-800-633-0405**



**Order Today,  
Ships Today!\***

**BEST INDUSTRIAL  
AUTOMATION DISTRIBUTOR**  
IEN Best Brand 2007

**AUTOMATIONDIRECT**.com  
the #1 value in automation

\* See our Web site for details and restrictions.  
© Copyright 2008 AutomationDirect, Cumming, GA USA. All rights reserved.