

Tools you need at low direct prices

It's time to try AutomationDirect!

Our shipping policies make it easier than ever to order direct from the U.S.!

Free standard ground shipping is available for orders totaling over \$300 U.S. (except for items which require LTL shipping, see Web site for details). Also, save on brokerage fees when shipping standard ground to Canada - you can choose to allow AutomationDirect to nominate a broker for your shipment for parts shipping via standard ground. This can save you big on brokerage fees. See Web site for details and restrictions - www.automationdirect.com/canada

WIRE

Choose from MTW, THHN and TFFN styles in the most common gauge sizes and colors



- 4 to 18 gauge wire in 500 and 2500-ft. reels
- All colors and sizes in stock, starting at \$29 for 500-ft. spool
- FREE shipping on orders over \$300 (shipped standard ground; LTL extra to Canada)

www.automationdirect.com/wire

TERMINAL BLOCKS

Signal and power terminal blocks for point-to-point wiring



- Screw-type terminal blocks in standard gray, plus seven colors for popular sizes
- Screwless terminal blocks also available
- Power distribution blocks, SCCR rated up to 200kA

www.automationdirect.com/terminal-blocks

WIRE DUCT & TUBING

Rigid and flexible wire duct & liquid-tight tubing



- All rigid duct comes in 2 meter lengths, with cover, sold individually or in value packs
- Flexible duct, braided sleeving and duct accessories available
- 30-meter liquid-tight tubing, coils in diameters from 3/8 to 2 inches

www.automationdirect.com/wiring-solutions

ENCLOSURES

Over 1,600 enclosures from Hubbell/Wiegmann



- NEMA 1, 3S, 3R, 4, 4X, 6P, 4/12 and 13 metallic enclosures
- Non-metallic line for harsh outdoor environments in NEMA 3R or 4X
- Steel and stainless flanged enclosures for disconnect mounting

www.automationdirect.com/enclosures

PUSHBUTTONS/LIGHTS

Choose from the HT800 30 mm metal NEMA series, 22 mm metal or non-metal IEC devices, and incandescent or bright stacklights for panel controls



- Flush, extended, illuminated or non-illuminated, mushroom and guarded pushbuttons, many available in multiple colors
- Pilot and push-to-test lights
- Selector switches in knob, lever and keyed versions
- Stacklights in modular or pre-assembled units

www.automationdirect.com/pushbuttons_lights

NEW!



JOBBER-LENGTH DRILL BITS

Our high performance twist drills are suitable for all normal drilling in conventional materials. Available in High Speed Steel (HSS) and Titanium Nitride-coated High Speed Steel, these drill bits are available in 1/16 to 1/2 inch hole sizes.

Jobber-length Drill Bits starting at **\$4.00 U.S.** (214801 pack of 10)

KNOCKOUT PUNCHES

Ruko's knockout punch hole-cutting tools include a punch, die and draw bolt. Use for sheet steel, stainless-steel sheets, non-ferrous and light metals, and plastics with a ball bearing washer to reduce cutting effort. Replacement bolts are offered in three popular sizes.

Knockout Punches starting at **\$20.75 U.S.** (109220)

SPLIT POINT STEP DRILL BITS

The spiral flutes of RUKO high-performance step drills are CBN-ground for a better and sharper cutting edge without burrs. Available in ranges to cut holes up to 1-1/8 inches, you won't find a better price on these high-precision tools.

Split Point Step Drill Bits starting at **\$14.75 U.S.** (101701)

MACHINE TAPS

Choose from 9 sizes in coarse or fine thread machine taps.

Machine Taps starting at **\$6.50 U.S.** (265040UNC)

www.automationdirect.com

For complete information or to order our free catalog, visit: www.automationdirect.com/tools

1-800-633-0405

**Order Today,
Ships Today!***

* See our website for exclusions.
© Copyright 2009 AutomationDirect, Cumming, GA USA. All rights reserved.

AUTOMATIONDIRECT.COM
the #1 value in automation