

Get more power for your dollar

It's time to try AutomationDirect!



Encapsulated Transformers
starting at
\$91.00 U.S.

Hammond encapsulated and control transformers

The new Fortress series of encapsulated transformers are single phase units available in 500VA up to 5 kVA ranges. The NEMA 3R enclosure makes them ideal for indoor and outdoor applications, such as schools, sports complexes, office buildings and lighting.

HPS Emperor control transformers are specifically designed for high inrush applications requiring reliable output voltage stability. New models expand the input and output voltage ranges available, all at low direct prices!



Control Transformers
starting at
\$30.00 U.S.



Control transformers with lifetime warranty

- NEW! MGJ Control Series: 50VA to 500VA, 380x277x208 primary, 240x120 secondary
- NEW! MLI Control Series: 50VA to 500VA, 480x240 primary, 120x25 secondary
- MQMJ Control Series: 50 VA to 1.5kVA, 230x460 primary, 115x230 secondary
- PG Control Series: 50VA to 1kVA, 120x240 primary, 24x12 secondary

Encapsulated Transformers

- NEW! Fortress series: 500VA to 5kVA, 480x240 primary, 240x120 secondary, NEMA 3R enclosure, 10-year warranty

www.automationdirect.com

For complete information or to order our free catalog, visit:
www.automationdirect.com/power-transformers

1-800-633-0405

Also Available:

POWER SUPPLIES

RHINO DC switching power supplies with 3-year warranty start as low as \$56.50 U.S.

New!
PSC series
NEC Class 2



- PSM metal series in 12 and 24 VDC adjustable output models from 78 to 600W
- PSP plastic-housed ultracompact series in 5, 12 and 24 VDC models up to 10A output current

www.automationdirect.com/dc-power-supplies

DC CONVERTERS

RHINO DC to DC converters isolate and regulate 5, 12 and 24 VDC power, starting at \$70.25 U.S.



- Input ranges from 9.5 to 18 VDC, 18 to 75VDC
- Output voltage adjustable

www.automationdirect.com/dc-converters

POWER DISTRIBUTION BLOCKS

Finger-safe style

- Accept copper conductors, maintain an SCCR rating of 200kA (with fusing)
- 175A to 760A ratings, starting at \$8.25



Open style

- Maintain an SCCR rating of 200kA with copper conductors and 10kA for aluminum conductors.
- Up to 760A ratings, starting at \$6.25
- One, two and three-pole models

www.automationdirect.com/power-blocks



**Order Today,
Ships Today!***

* See our website for exclusions.
© Copyright 2009 AutomationDirect, Cumming, GA USA. All rights reserved.

AUTOMATIONDIRECT.com
the #1 value in automation