

Get more control with less energy

with our AC and DC drives



STARTING AT:
\$156 U.S.
GS2-10P2

STARTING AT:
\$99 U.S.
GS1-10P2

STARTING AT:
\$242 U.S.
GS3-21P0



DURA
IIII PULSE

High-quality AC drives pay for themselves in a hurry

Variable speed drives can improve your bottom line by reducing your motors' energy consumption. An investment of as little as \$99 can start paying off immediately.

- GS1 AC drives (1/4 to 2 hp) offer simple Volts/Hz control for general purpose applications. Built-in I/O, Modbus communications capability and programmable preset speeds increase its flexibility.
- GS2 AC drives (0.5 to 10 hp) feature built-in PID control, dynamic braking and Modbus communications.
- DuraPULSE AC drives (1 to 100 hp) add sensorless vector control, a removable keypad that stores up to four different application programs and built-in discrete and analog I/O. Communicate via built-in Modbus or an optional Ethernet connection.

DC drives for efficient control

Ironhorse DC drives are suitable for many control applications, all at prices that won't break your budget.

- Excellent low speed control and stability
- Configured with potentiometers – no parameters or programming needed
- DC motors coupled with DC drives provide exceptional low speed torque and power



STARTING AT:
\$59 U.S.
GSD3-240-2CL

IRONHORSE

Research, price, buy at:
www.automationdirect.com/drives

Also Available

LR Series
Line Reactors



High-Speed
Class J Fuses



AC Motor
Soft Starters



Optional Drive
Related Items



Replacement
Fans



Order Today, Ships Today!

* See our Web site for details and restrictions. © Copyright 2014 AutomationDirect, Cumming, GA USA. All rights reserved.



AUTOMATIONDIRECT.com
1-800-633-0405

the #1 value in automation