

Stainless Steel AC Motors

... with IP56 environmental rating



IRONHORSE

Starting at
\$275.00 U.S.
MTSS-P33-3BD1BR



Ready for washdown and harsh environments!

IronHorse™ Stainless Steel AC motors are designed for use in applications where motors are frequently exposed to moisture, humidity, certain chemicals or other washdown environments. (*NOT rated for direct contact with food.*) All our Ironhorse motors are in stock and ready for **same-day** shipment; if your order is over \$49, you get **free shipping** too!

Also Available



- **Cast Iron Premium Efficiency motors** up to 200 hp, starting at \$155



- **Single-phase and three-phase rolled steel general purpose motors** up to 2 hp, starting at \$79



- **Marathon Inverter-duty AC motors** up to 100 hp, starting at \$143



- **DC motors** up to 2 hp, starting at \$133

Features

- 0.33 to 2 hp, three-phase
- 1800 and 3600 RPM
- Standard NEMA 56C frame
- Available with or without mounting feet
- Totally enclosed, fan cooled
- 304 stainless frame and base; 303 stainless motor shaft
- No restriction on mounting orientation
- IP66 cord grip included

www.automationdirect.com/motors



<http://bit.ly/adcmotors>

www.automationdirect.com

Go online or call to get complete information, request your free catalog, or place an order.

1-800-633-0405



**Order Today,
Ships Today!**

* See our Web site for details and restrictions.
© Copyright 2012 AutomationDirect, Cumming, GA, USA. All rights reserved.



AUTOMATIONDIRECT.com

the #1 value in automation