

Precision Regulators Priced Right!

Precision Regulators

Get durable, high-precision pressure regulators, in a variety of pressure ranges, at incredible prices from AutomationDirect. These affordable regulators offer numerous flow options up to 200 SCFM and sensitivity as low as 1/8" water (0.0045psi). Miniature versions are also available with high levels of regulation accuracy in a compact, lightweight housing.



Precision Combination Filter/Regulators

Get clean, accurate instrument air, all-in-one, with the new NITRA precision combination filter/regulator. Ideal for industrial environments, these combination regulators are built to last and priced right!



NITRA
PNEUMATICS

Also Available

Modular Regulators & Combination Filter/Regulators



NITRA pneumatic air pressure regulators and combination regulators are available in a wide selection of port sizes with adjustable pressure ranges to meet a broad range of pneumatic applications.

Soft Start Valves



NITRA dependable soft-start/dump valves protect your downstream equipment from unwanted stress and damage by gradually increasing system pressure.

Manual Relief Valves



NITRA pneumatic manual shut-off pressure relief valves have a small, modular design that allows for easy field assembly and provide needed pressure relief with lock out capabilities.

NEW!

Potable Water Pressure Regulators



HydroMode FR Series food grade regulators are compact units that provide economical, high-performance pressure regulation of drinkable water.

Research, price, buy at:

www.automationdirect.com/pneumatic-FRL

Order Today, Ships Today!



AUTOMATIONDIRECT.com
1-800-633-0405 the #1 value in automation

*See our Web site for details and restrictions. © Copyright 2014 AutomationDirect, Coalinga, CA, USA. All rights reserved.