

# Mechanical Pressure Switches

at AutomationDirect prices

**NEW!**

## Under pressure? Rugged and reliable switches will perform!

The ProSense MPS25 series mechanical pressure switches are designed for the toughest applications where conventional pressure switch designs often don't measure up. These cost effective switches, depending on the pressure range, have either an all welded 316 stainless steel sealed diaphragm actuator design or a direct acting 316 stainless steel piston design with a Buna-N O-ring.

- Ranges available from -15 psi vacuum to 7,500 psi
- Tamper-resistant field setpoint adjustment
- 1/4-inch NPT mail process connection
- Models with 6-foot embedded cable with 1/2-inch NPT conduit connection, or DIN form C electrical connection

These pressure switches are ideal for applications such as:

- Process control
- Pump and compressor control
- Pneumatic systems

Research, price, buy at:

[www.automationdirect.com/  
pressure-switches](http://www.automationdirect.com/pressure-switches)

Adjustment cover open

**\$82.00**  
for DIN Form C  
connector models

**\$89.00**  
for 6-foot embedded  
cable models

## Also Available

Pressure & Differential Transmitters



Flow Switches



Temperature Sensors & Transmitters



Digital Pressure Switches



Level Sensors



Solo™ Process Controllers



**Order Today, Ships Today!**

\* See our Web site for details and restrictions. © Copyright 2013 AutomationDirect, Cumming, GA USA. All rights reserved.



**AUTOMATIONDIRECT**.com

1-800-633-0405

the #1 value in automation