

IP69K sensors for extreme conditions

at AutomationDirect prices



When you need sensors for harsh environments, these IP69K rated models give you supreme performance at prices you can't beat!

Proximity

- All sensors feature 316L stainless steel housings and quick-disconnect plugs
- Inductive models - 12, 18 and 30mm DC, and 18 and 30mm AC - with sensing ranges up to 22mm
- 12 and 18mm DC magnetic models with sensing ranges up to 70mm
- 2-, 3- and 4-wire output configurations

Photoelectric

- All sensors feature 316L stainless steel housings and quick-disconnect plugs
- 18mm threaded round with diffuse, polarized reflective, retroreflective, through-beam or diffuse with background suppression sensing
- Up to 20 meter sensing range

Quick-disconnect cables

- IP69K-rated cables in five and 10-meter lengths
- Axial or right angle optics
- M12 or half-inch micro connector ends

Along with our great prices, you get:

- Same-day shipping (when ordered by 6 pm EST, with approved credit or credit card, see Web site for details)
- FREE 2-day (or less) delivery on most orders over \$300
- Free award-winning Tech Support
- 30-day money-back guarantee!

IP69K SENSORS

CHECK OUT OUR PRICES AutomationDirect

12mm DC inductive proximity with M12 Q/D, 4mm sensing distance	\$35.00 PFM1-AP-3H
18mm DC diffuse photoelectric, M12 Q/D, 100mm sensing distance	\$65.00 FFR3-BN-1E
M12 cable for Q/D sensors, 12mm axial female, IP69K, 5 meter	\$12.50 EVT221

*All prices are U.S. published prices. AutomationDirect prices are October 2011 prices.

www.automationdirect.com/sensors

www.automationdirect.com

Go online or call to get complete information, request your free catalog, or place an order.

1-800-633-0405



**Order Today,
Ships Today!***

* See our Web site for details and restrictions.
© Copyright 2012 AutomationDirect, Cumming, GA USA. All rights reserved.



AUTOMATIONDIRECT.com
the #1 value in automation