

DRIVE In Efficiency, DRIVE Out Cost.

AC and DC drives at great prices



Volts/Hertz AC Drives

GS1 & GS2 Series starting at \$99.00

- Dynamic braking & PID control
- Support for analog and discrete input, plus relay output
- Removable/relocatable keypad (GS2)
- RS-485 MODBUS communication
- Single and three-phase input
- 1/4 to 10 HP



Sensorless Vector AC Drives

Durapulse® Series starting at \$242.00

All GS series features (above) plus:

- Sensorless vector control w/autotune
- Supports optional encoder feedback for enhanced speed control
- Smart keypad stores all parameters
- Three-phase models: 1 to 100 HP
- Single-phase input on select models



Soft Starters for AC Motors

Stellar® Series starting at \$119.00

- Three-phase models from 5A to 477A
- Intelligent Energy Recovery System (IERS) reduces power consumption
- Reduced mechanical stress extends the life of the machinery
- Fast setup for a wide range of applications



Ironhorse® DC Drives

Starting at \$60.00

- Input voltages: 12/24/36/48 VDC 12/24 VAC, 24/36 VAC, 115/230 VAC and 120/240 VDC
- Output voltages: 12/24/36/48/90/180 VDC
- Output current up to 20A
- Available in open frame and NEMA rated enclosed versions



Also Available

DC Motors and Gearmotors

AC Motors

Fuses, Filters, Line Reactors, Braking Units and more...



Research, price, buy at:
www.go2adc.com/drives



AUTOMATIONDIRECT.com

1-800-633-0405

the #1 value in automation