

Get in gear!

with Ironhorse gearboxes

IronHorse worm gearboxes are manufactured using only the highest quality materials and are designed to withstand the toughest international and U.S. testing standards. Our gearboxes interface with C-face motors and provide reliable speed reduction, increased torque and dual load capabilities wherever it is needed.



IRONHORSE®

Cast Iron Gearboxes

Cast-iron gearboxes are available with right-hand and dual (both right and left) output shafts, and hollow-bore outputs.

Features

- **Three output types: Dual Shaft, Right Hand Shaft and Hollow Shaft**
- **Four frame sizes: 1.75", 2.06", 2.37", 2.62" models with parallel or right-angle gear shafts**
- **Six ratios: 5:1, 10:1, 15:1, 20:1, 40:1, 60:1**
- **One-piece cast iron gear box housing, 1045 carbon steel shaft**
- **Double-lipped embedded oil seals to prevent gearbox leakage**
- **Universally interchangeable compact design ensures easy OEM replacement**
- **One year warranty**

NEW! Aluminum Gearboxes

Our new aluminum gearboxes are lightweight and durable, built with hardened steel worm shafts and hollow-bore outputs.

Features

- **Five frame sizes: 30, 40, 50, 63, 75 mm**
- **Two ratios: 10:1 to 100:1 (in most sizes)**
- **Input faces: 56C, 145TC, 182/4TC reversible design**
- **Aluminum alloy housing for lightweight design**
- **Two bearings on input and output shafts**
- **Double-lipped embedded oil seals to prevent gearbox leakage**
- **Multiple mounting holes for all angle mounts**
- **One year warranty**

Starting at:
\$147.00

Starting at:
\$88.00

Cast Iron Premium
Efficiency Motors



Rolled Steel General
Purpose Motors



Inverter-Duty
AC Motors



Also Available

Research, price, buy at: www.automationdirect.com/power-transmission

Order Today, Ships Today!

* See our Web site for details and restrictions. © Copyright 2014 AutomationDirect, Cumming, GA USA. All rights reserved.



AUTOMATIONDIRECT.com
1-800-633-0405

the #1 value in automation