

High Level Control

at low level prices

NEW!

Level Controllers

Flowline Switch-Pro™ and DataPoint™ Remote Level Controllers provide continuous liquid level control with the accuracy and dependability you need. The fail-safe relay design can be configured for alarming and/or automatic fill/empty control using valves and pumps for a closed-loop system.

- 35mm DIN rail mount or panel mount polypropylene (PP) enclosure with removable terminal strips
- Relay control of pumps or valves with 0-60 second delay
- LED indicators for sensor, power and relay status (LC40, LC41 and LC42 models)
- 3.5 digit LED display indicates level in custom engineering units (LC52 model)
- Invert switch changes relay state from NO to NC without rewiring

Starting at:
\$181.00



FLOWLINE®

Also Available



Flowline non-contact ultrasonic liquid level sensors use proven technology that won't fail because of dirty, sticky or scaling liquids.



Flowline Switch-Tek™ Level Sensors provide reliable liquid level detection for a wide range of materials and applications.



ProSense SLT series submersible level sensors provide continuous, precise liquid level measurement using the hydrostatic pressure exerted by the liquid above the sensor.



ProSense float level switches provide a low-cost general purpose solution for single point monitoring of liquid level in a variety of applications.

Research, price, and buy at: www.automationdirect.com/level-sensors

Order Today, Ships Today!

* See our Web site for details and restrictions. © Copyright 2014 AutomationDirect, Cumming, GA USA. All rights reserved.



AUTOMATIONDIRECT.com
1-800-633-0405

the #1 value in automation