

Process Sensing

from top to bottom

PRESSURE

ProSense pressure switches and sensors monitor hydraulic, pneumatic and other process applications reliably and accurately. A wide selection of models are available:

- Mechanical or electronic pressure switches for low-cost indication and switching
- Gauge and vacuum pressure transmitters with ceramic or stainless steel sensing elements
- Digital pressure switches/transmitters with integral LCD display
- Air differential sensors also available

Starting at:
\$69.00



LEVEL

Flowline non-contact ultrasonic liquid level sensors use proven technology that won't fail because of dirty, sticky or scaling liquids.

Starting at:
\$260.00



- Continuous level measurement, switching and level control
- Automatic temperature compensation for accurate measurement
- Output options include current, voltage, frequency and relay
- Pushbutton configured models, or PC configured models using free software

TEMPERATURE

ProSense family of temperature sensing components includes:



Starting at:
\$15.25

- Thermocouple and RTD probes and sensors
- Transmitters with integral sensors, or thermocouple or RTD input
- Thermowells and fittings
- Thermocouple and RTD extension wire

FLOW

The ProSense FSD Series flow switches monitor liquid media and provide reliable flow detection for industrial applications.

Starting at:
\$125.00



- Ranges available up to 26.4 GPM
- Fast 10ms response time
- Easy-to-turn dial to choose setpoint
- Integrated check valve prevents back flow in horizontal or vertical mounting
- LED output status indicator
- IP65 / IP67

Research, price, and buy at
www.automationdirect.com/process-controllers

Order Today, Ships Today!



AUTOMATIONDIRECT.com
1-800-633-0405

the #1 value in automation

* See our Web site for details and restrictions. © Copyright 2013 AutomationDirect, Cumming, GA USA. All rights reserved.