

Save on energy costs

NEMA Premium AC motors

Get high-quality motors at AutomationDirect prices!

Marathon Electric NEMA Premium Efficiency XRI series motors are compliant with the Energy Independence and Security Act of 2007. These motors offer you both low purchase prices and long-term energy savings. Our line of Marathon motors includes:

- **NEMA Premium Efficiency XRI (1 - 10 hp)**, starting at \$310
- **Blue Chip XRI Ultra High Efficiency (15 - 100 hp)**, for high-cycle or long-run applications, starting at \$993
- **Inverter-duty (1/4 to 100 hp) standard efficiency**, starting at \$129

IronHorse® AC and DC motors

AutomationDirect's IronHorse line of general purpose motors and gearboxes comes from a manufacturer who has nearly three decades of solid experience and reliability in the North American motor market. When you combine that with our great pricing, same-day shipping* and award-winning service, you have a winning combination!

- **High Efficiency cast iron T frame AC motors (1 - 300 hp)**, starting at \$108
- **High Efficiency cast iron TC frame AC motors (1 - 100 hp)**, starting at \$130
- **Single and three-phase rolled steel 56C frame AC motors (0.33 to 2 hp)**, starting at \$70
- **DC motors (0.33 to 2 hp)**, starting at \$119

All IronHorse motors are backed by a two-year warranty and a 30-day money-back guarantee. Does your current supplier do that?

Visit : www.automationdirect.com/motors

www.automationdirect.com

Go online or call to get complete information, request your free catalog, or place an order.

1-800-633-0405

**Order Today,
Ships Today!***

* See our Web site for details and restrictions.
© Copyright 2010 AutomationDirect, Cumming, GA, USA. All rights reserved.



AUTOMATIONDIRECT.com
the #1 value in automation

