

Pneumatic Gripper - Angular (Side Mount Grip)

Double Acting



KA06MD-M

NITRA Pneumatics grippers are an excellent choice for many automation applications. They are available in both parallel and angular travels in seven different body sizes. Grippers are either double acting, single acting normally closed or single acting normally open. Anodized aluminum bodies include integral mounting slots for position switches.

Features

- Six sizes available (6 to 32mm bore)
- Double acting or single acting N.O.
- Anodized aluminum bodies
- Position switch ready with integral mounting slots



NITRA Pneumatic Gripper - Angular - Double Acting										
Part No.	Description	Style	Action	Size - Bore (mm)	Position	Grip	Body	Port(s)	Price	Weight (lbs)
KA06MD-M	NITRA pneumatic gripper	Angular	Double acting	6	30 degrees open, -10 degrees closed	Side mount Anod		M3 x 0.5	\$67.00	0.1
KA10MD-M				10					\$94.00	0.2
KA16MD-M				16			Anodized	M5 x 0.8	\$97.00	0.3
KA20MD-M				20		grip	rip aluminum		\$117.00	0.5
KA25MD-M				25					\$130.00	1.0
KA32MD-M				32					\$144.00	1.9

NITRA Pneumatic Gripper Specifications						
Fluid		Air (clean/dry)				
Pressure Range		All double acting models: 22 to 101 psig (1.52 to 6.97 bar)				
Temperature Ran	ge	-4°F to 160°F (-20°C to 60°C)				
Lubrication		Cylinder: not required - Jaws: grease regularly				
Cushion Type		Bumper				
Integrated Flow Control	6mm	N/A				
	10mm to 32mm	Standard - flow control in closing direction				
Maximum Freque	ncy	180 cycles/min				
Port Size		M3 x 0.5 (6mm to 10mm units) M5 x 0.8 (16mm to 32mm units)				
Sensor Switch Co	mpatibility	Nitra CPS9H-xx-x or CPS9C-xx-x				
Includes		Magnet				
Approvals		None				



See <u>www.automationdirect.com</u> for our online Configuration Tool for further selection assistance.


tPNE-266 Pneumatics 1 - 8 0 0 - 6 3 3 - 0 4 0 5





Pneumatic Gripper - Angular (Side Mount Grip)

Dimensions

mm [inches]







Pneumatic Gripper Dimensions									
Part #	Α	В	С	ØD					
KA06MD-M	47.5 [1.87]	20.0 [0.79]	10.5 [0.41]	M3 x 0.5					
KA10MD-M	52.5 [2.07]	23.0 [0.91]	16.5 [0.65]	M3 x 0.5					
KA16MD-M	62.5 [2.46]	30.5 [1.20]	23.5 [0.93]	M5 x 0.8					
KA20MD-M	78.0 [3.07]	42.0 [1.65]	27.5 [1.08]	M5 x 0.8					
KA25MD-M	92.0 [3.62]	52.0 [2.05]	33.5 [1.32]	M5 x 0.8					
KA32MD-M	96.5 [3.80]	60.0 [2.36]	40.0 [1.57]	M5 x 0.8					

See our website $\underline{\textit{www.AutomationDirect.com}}$ for complete Engineering drawings.



Pneumatic Gripper - Angular (Side Mount Grip)

Single Acting - Normally Open



KA06MSA-M

NITRA Pneumatics grippers are an excellent choice for many automation applications. They are available in both parallel and angular travels in seven different body sizes. Grippers are either double acting, single acting normally closed or single acting normally open. Anodized aluminum bodies include integral mounting slots for position switches.

Features

- Six sizes available (6 to 32mm bore)
- Double acting or single acting N.O.
- Anodized aluminum bodies
- Position switch ready with integral mounting slots



NITRA Pneumatic Gripper - Angular - Normally Open										
Part No.	Description	Style	Action	Size - Bore (mm)	Position	Grip	Body	Port(s)	Price	Weight (lbs)
KA06MSA-M	NITRA pneumatic gripper	Angular	Single acting, normally open	6	30 degrees open, -10 degrees closed		Anodized	M3 x 0.5	\$67.00	0.1
KA10MSA-M				10					\$94.00	0.2
KA16MSA-M				16				M5 x 0.8	\$97.00	0.3
KA20MSA-M				20			aluminum		\$117.00	0.5
KA25MSA-M				25					\$130.00	1.0
KA32MSA-M				32					\$144.00	1.9

NITRA Pneumatic Gripper Specifications						
Fluid		Air (clean/dry)				
Dragouro Dongo	6mm	45 to 101 psig (3.10 to 6.97 bar)				
Pressure Range	10mm to 32mm	36 to 101 psig (2.48 to 6.97 bar)				
Temperature Rang	ge	-4°F to 160°F (-20°C to 60°C)				
Lubrication		Cylinder: not required - Jaws: grease regularly				
Cushion Type		Bumper				
Integrated Flow Control	6mm	N/A				
	10mm to 32mm	Standard - flow control in closing direction				
Maximum Frequency		180 cycles/min				
Port Size		M3 x 0.5 (6mm to 10mm units) M5 x 0.8 (16mm to 32mm units)				
Sensor Switch Co.	mpatibility	Nitra CPS9H-xx-x or CPS9C-xx-x				
Includes		Magnet				
Approvals		None				



See <u>www.automationdirect.com</u> for our online Configuration Tool for further selection assistance.


tPNE-268 Pneumatics 1 - 8 0 0 - 6 3 3 - 0 4 0 5




Pneumatic Gripper - Angular (Side Mount Grip)

Dimensions

mm [inches]







Pneumatic Gripper Dimensions									
Part #	Α	В	С	ØD					
KA06MSA-M	47.5 [1.87]	20.0 [0.79]	10.5 [0.41]	M3 x 0.5					
KA10MSA-M	52.5 [2.07]	23.0 [0.91]	16.5 [0.65]	M3 x 0.5					
KA16MSA-M	62.5 [2.46]	30.5 [1.20]	23.5 [0.93]	M5 x 0.8					
KA20MSA-M	78.0 [3.07]	42.0 [1.65]	27.5 [1.08]	M5 x 0.8					
KA25MSA-M	92.0 [3.62]	52.0 [2.05]	33.5 [1.32]	M5 x 0.8					
KA32MSA-M	96.5 [3.80]	60.0 [2.36]	40.0 [1.57]	M5 x 0.8					

See our website $\underline{\textit{www.AutomationDirect.com}}$ for complete Engineering drawings.