

ABB Ty-Grip® Reusable Cable Ties

Overview

Ty-Grip cable ties offer a reusable and adjustable solution for organizing cables and wires where bundles need to be accessed, reconfigured, or repositioned frequently. Made from nylon and polyethylene, these ties fasten securely without tools and release cleanly without damaging cable insulation. Available in four form factors to suit different installation requirements.

Ty-Grip cable ties are ideal for data centers, AV installations, laboratory equipment, and anywhere organized cable management must remain accessible. The roll format allows ties to be cut to any length on site, providing maximum flexibility for large or irregular bundles.



Features

- Reusable and adjustable
- Tool-free installation and removal
- Rounded edges to avoid cable damage
- Operating temperature: -4 to +219 °F [-20 to +104 °C]
- Minimum installation temperature: -4 °F [-20 °C]
- Black

Agency Approvals

- CE

| Roll-Type Reusable Cable Ties | | | | | | | | | | | | |
|-------------------------------|----------------|----------|---------|-----------------------|--------|-----|-------|------|---------------|----|------------------|----|
| Part Number | Cable Tie Type | Pcs/ Bag | Price | Material | Length | | Width | | Max. Bundle Ø | | Tensile Strength | |
| | | | | | m | in | mm | in | mm | in | kg | lb |
| FOR180-50-0 | Roll | 1 | \$42.50 | Nylon Polyethylene | 4.57 | 180 | 19.05 | 0.75 | - | - | 23 | 50 |



[FOR180-50-0](#)

| Slotted Reusable Cable Ties | | | | | | | | | | | | |
|-----------------------------|----------------|----------|---------|-----------------------|--------|----|-------|------|---------------|-----|------------------|----|
| Part Number | Cable Tie Type | Pcs/ Bag | Price | Material | Length | | Width | | Max. Bundle Ø | | Tensile Strength | |
| | | | | | mm | in | mm | in | mm | in | kg | lb |
| FO200-40-0 | Slotted | 10 | \$19.50 | Nylon Polyethylene | 228.60 | 9 | 12.70 | 0.5 | 50.80 | 2 | 18 | 40 |
| FO200-50-0 | Slotted | 10 | \$29.50 | | 228.60 | 9 | 19.05 | 0.75 | 50.80 | 2 | 23 | 50 |
| FO350-40-0 | Slotted | 10 | \$26.00 | | 330.20 | 13 | 12.70 | 0.5 | 88.90 | 3.5 | 18 | 40 |
| FO350-50-0 | Slotted | 10 | \$43.50 | | 330.20 | 13 | 19.05 | 0.75 | 88.90 | 3.5 | 23 | 50 |



[FO200-40-0](#)

| Buckle Reusable Cable Ties | | | | | | | | | | | | |
|-----------------------------|----------------|----------|---------|----------|--------|----|-------|------|---------------|----|------------------|----|
| Part Number | Cable Tie Type | Pcs/ Bag | Price | Material | Length | | Width | | Max. Bundle Ø | | Tensile Strength | |
| | | | | | mm | in | mm | in | mm | in | kg | lb |
| FOL300-50-0 | Buckle | 10 | \$30.50 | Nylon | 304.80 | 12 | 19.05 | 0.75 | 76.20 | 3 | 23 | 50 |
| FOL500-50-0 | Buckle | 10 | \$38.00 | | 457.20 | 18 | 19.05 | 0.75 | 127.00 | 5 | 23 | 50 |



[FOL300-50-0](#)

Note: These parts have an operating temperature of -4 to +199.4 °F [-20 to +93 °C]

| Strip Reusable Cable Ties | | | | | | | | | | | | |
|-----------------------------|----------------|----------|---------|-----------------------|--------|----|-------|------|---------------|-----|------------------|----|
| Part Number | Cable Tie Type | Pcs/ Bag | Price | Material | Length | | Width | | Max. Bundle Ø | | Tensile Strength | |
| | | | | | mm | in | mm | in | mm | in | kg | lb |
| FOS150-50-0 | Strip | 10 | \$15.00 | Nylon Polyethylene | 152.40 | 6 | 19.05 | 0.75 | 38.10 | 1.5 | 23 | 50 |
| FOS320-50-0 | Strip | 10 | \$22.50 | | 304.80 | 12 | 19.05 | 0.75 | 81.28 | 3.2 | 23 | 50 |



[FOS150-50-0](#)